




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



| PANDUIT<br>PART NO.<br>(*) | WEIGHT<br>lbs / 100<br>(g) / pcs.                            |
|----------------------------|--------------------------------------------------------------|
| ABMT-_-_-                  | NO ADHESIVE<br>0.64 (291.4)<br>WITH ADHESIVE<br>0.65 (294.8) |



SCALE: FULL

#### NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND COLOR.
- A SUFFIX REPRESENTS RUBBER ADHESIVE  
-AT SUFFIX REPRESENTS ACRYLIC ADHESIVE  
-S6 SUFFIX, NO ADHESIVE: SCREW APPLIED WITH A #6-32 BUTTON HEAD CAP SCREW.
- ABMT-A HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 120°F (49°C).  
ABMT-AT HAS A MAXIMUM CONTINUOUS OPERATING TEMPERATURE OF 180°F (82°C).

|                                                                                                                                     |                                                                                               |
|-------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------|
| DIMENSIONS IN BRACKETS ARE METRIC [mm]                                                                                              |                                                                                               |
| G02471CB_PB_ABMT_01                                                                                                                 |                                                                                               |
| <b>PANDUIT</b> CORP. TINLEY PARK, ILLINOIS<br>ADHESIVE BACKED "TAK-TY" MOUNT<br>(ABMT-_-_-)                                         |                                                                                               |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE:<br>(.X) ±0.05 (1.3) (.XXX) ±0.010 (0.25)<br>(.XX) ±0.02 (0.5) ANGLES ±5° | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN<br>IN INCHES, THIRD ANGLE PROJECTION. |
| DRAWN BY JAD                                                                                                                        | MAT'L: NYLON 6/6                                                                              |
| DATE 1/28/02                                                                                                                        | SCALE NONE                                                                                    |
| CHK'D                                                                                                                               | DRAWING NO. GB2471CB                                                                          |
|                                                                                                                                     | DWG SIZE A                                                                                    |

|     |         |     |     |               |          |   |      |     |  |
|-----|---------|-----|-----|---------------|----------|---|------|-----|--|
| 1   | 2/11/05 | JAD |     | 1.12 was 1.10 | GB2471CB | 1 |      |     |  |
| REV | DATE    | BY  | CHK | DESCRIPTION   | ECN      | R | CUST | SUP |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[ABMT-S6-C20](#) [ABMT-S6-Q20](#) [ABMT-S6-Q](#) [ABMT-S6-Q69](#)