

A.
Featured
Products

B.
Copper
Systems

C.
Fiber
Systems

D.
Faceplates,
Frames &
Surface
Mount Boxes

E.
Industrial
Networks

F.
Audio
Video
Systems

G.
Keystone
Cabling
Systems

H.
Zone
Cabling

J.
Cable
Routing
Systems

K.
Surface
Raceway

L.
Cabinets
& Rack
Systems

M.
Power
Management

N.
Grounding
& Bonding

O.
Identification
Products

P.
Cable
Management
Accessories

Q.
Part
Number
Index

€ Tak-Ty® Hook & Loop Cable Ties

- Soft, premium material is safe to use on high performance network cables protecting against over-tensioning
- Broad selection of durable designs and sizes
- Adjustable, releasable, and re-usable hundreds of times – ideal for applications requiring frequent moves, adds, or changes
- Easy to use and operator safe with no sharp edges
- A full range of colors
- Operating temperature range: 0°F to 220°F (-18°C to 104°C)
- Complementary mounts available



HLT (Loop Ties)





HLS (Strip Ties)



HLB (Stacked Strips)



HLM/HLS (Rolls)



Part Number	Length		Width		Max. Bundle Dia.		Min. Loop Tensile Strength*		Std. Pkg. Qty.	Std. Ctn. Qty.
	In.	mm	In.	mm	In.	mm	Lbs.	N		

Loop Ties – Slot allows for pre-wrapping of bundles

HLT2I-X0	8.00	203.0	0.50	12.7	1.91	49.0	40	178	10	100
HLT3I-X0	12.00	305.0			3.18	81.0				
HLT2I-M0	8.00	203.0			1.91	49.0			1	1
HLT3I-M0	12.00	305.0			3.18	81.0				

Strip Ties – Perforated in convenient 6", 12", and 18" strips

HLS1.5S-X0	6.00	152.0	0.75	19.1	1.50	38.0	50	222	10	100
HLS3S-X0	12.00	305.0			3.20	81.0				
HLS5S-X0	18.00	457.0			5.00	127.0				

Stacked Strip Ties – Eliminates cutting ties to length and staging them for each job Rounded edges for installer safety – 100 pieces

HLB2S-C0	7.00	178.0	0.75	19.1	1.60	41.0	50	222	1	10
----------	------	-------	------	------	------	------	----	-----	---	----

Part Number	Length		Width		Max. Bundle Dia.		Min. Loop Tensile Strength*		Std. Pkg. Qty.	Std. Ctn. Qty.
	Ft.	m	In.	mm	In.	mm	Lbs.	N		

15' and 75' Continuous Rolls – Can be cut to desired length, eliminating waste

HLM-15R0	15.0	4.6	0.33	8.4	Various	Various	18	80	1	10
HLS-15R0			0.75	19.1			50	222		
HLS-75R0	75.0	22.9								

For color options, reference hook and loop cable ties chart, see page P.5.

*Note: Minimum 2" overlap required to achieve loop tensile rating.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[HLS-15R0](#) [HLS3S-X5](#) [HLS3S-X0](#) [HLT3I-X0](#) [HLS-15R2](#) [HLS-15R5](#) [HLS-15R6](#) [HLS-15R8](#) [HLS1.5S-X10](#) [HLT2I-X2](#) [HLT2I-X6](#) [HLB2S-C0](#) [HLS-75R2](#) [HLS-15R10](#) [HLB2S-C5](#) [HLB2S-C6](#) [HLM-15R2](#) [HLM-15R4](#) [HLS1.5S-X4](#) [HLS1.5S-X5](#) [HLS5S-X6](#) [HLT3I-M0](#) [HLS1.5S-X3](#) [HLS5S-X8](#) [HLS1.5S-X8](#) [HLT2I-X8](#) [HLS-75R10](#) [HLS5S-X5](#) [HLS5S-X10](#)