


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

| Part Number    | Width<br>in. (mm) | Length<br>ft. (m) | Thickness<br>in. (mm) | Package<br>per Roll | Description                                           | Insulation<br>Color | Weight<br>oz. (gram) |
|----------------|-------------------|-------------------|-----------------------|---------------------|-------------------------------------------------------|---------------------|----------------------|
| ST14-075-60BK  | .75 (19)          | 60 (18)           | .007 (.18)            | CELLO WRAP          | General Purpose ST14 Black, .75" x 60'X .007"         | BLACK               | 2.9 (82)             |
| ST14-075-60BKX | .75 (19)          | 60 (18)           | .007 (.18)            | CELLO WRAP          | General Purpose ST14 Black, 10 pcs, .75" x 60'X .007" | BLACK               | 29 (820)             |

TAPE  
WIDTH



TAPE  
THICKNESS



**LISTED**  
Electrical Insulating Tape



**CERTIFIED**

- NOTES:
- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
  - ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
  - MATERIAL: RUBBER ADHESIVE PRESSURE SENSITIVE VINYL TAPE.
  - TEMPERATURE RATING: -10 °C TO 80 °C.
  - DIELECTRICAL STRENGTH: 7000V.
  - FLAME RETARDANT.
  - MEETS UL-510 AND CSA C 22.2 NO. 197.
  - COMPLIANT TO CALIFORNIA PROP. 65

|                                                                                  |            |           |       |                |  |                                                  |  |
|----------------------------------------------------------------------------------|------------|-----------|-------|----------------|--|--------------------------------------------------|--|
| PART NUMBER                                                                      |            | SEE TABLE |       | PACKAGING SPEC |  | PKG-516                                          |  |
| PRODUCT SPEC                                                                     |            | PS-SH-002 |       |                |  |                                                  |  |
| TITLE                                                                            |            |           |       |                |  |                                                  |  |
| Stronghold Insulating Tape-General Purpose ST14 Tape                             |            |           |       |                |  |                                                  |  |
| CUSTOMER DRAWING                                                                 |            |           |       |                |  |                                                  |  |
| ITEM REVISION NAME                                                               |            |           |       | 00351EBS/00    |  |                                                  |  |
| DATASET FILE NAME                                                                |            |           |       | 00351EBS_DC/00 |  |                                                  |  |
| UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN (mm)               |            |           |       |                |  | <b>PANDUIT</b><br><br>MATERIAL:<br><br>SEE NOTE3 |  |
| .x ± .1 [ 2.54 ]      .xxx ± .005 [ .127 ]<br>.xx ± .01 [ .25 ]      ANGLES ± 1° |            |           |       |                |  |                                                  |  |
| THIRD ANGLE<br>PROJECTION                                                        |            |           |       |                |  | DRAWING NUMBER:                                  |  |
|                                                                                  |            |           |       |                |  | 00351EBS_DC                                      |  |
| DRAWN BY                                                                         | DATE       | CHK       | SCALE | SHT 1 OF 1     |  | SIZE                                             |  |
| JSUN                                                                             | 04/29/2019 | ADAH      | NONE  |                |  | A                                                |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[ST14-075-60BK](#) [ST14-075-60BKX](#)