



- NOTES:
1. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
 2. DIMENSIONS IN [] ARE METRIC.
 3. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
 4. TOOL TO BE USED WITH CT-902HP OR CT-2902BPHP HYDRAULIC PUMP AND CT-900HPH HYDRAULIC HOSE ASSEMBLY OR SIMILAR HYDRAULIC SYSTEM GENERATING 10,000 PSI.
 5. WEIGHT: 15.0 LBS (6.8 KG.)
 6. DIMENSIONS: 14.5"L X 4.1"H X 2.5"W
(368mm L X 104mm H X 64mm W)
 7. TOOL OUTPUT: 15 TONS (13.6 METRIC TONS)
 8. PART INCLUDES:
CRIMP HEAD, OPERATING INSTRUCTIONS AND CARRYING CASE.
 9. ACCESSORIES AVAILABLE:
CT-940CHHAN, CRIMP HEAD HANDLE ASSEMBLY (SHOWN BELOW)
 10. APPLICABLE PANDUIT CONNECTOR RANGE:
#8 AWG - 1500MCM COPPER
#6 - 1000MCM ALUMINUM
 11. DO NOT USE ON LIVE CIRCUITS.
 12. DO NOT OPERATE TOOL WITHOUT DIES IN PLACE.
 13. TOOL TO BE USED WITH PANDUIT CD-940 SERIES DIES AND CAN ALSO BE USED WITH CD-920/CD-930 SERIES DIES WITH CD-940-DA DIE ADAPTER, P/N TP22447B01.



CRIMP HEAD

HANDLE ASSEMBLY

00	7-10-18	BJPU	SKB	JADE	INITIAL RELEASE	034305
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

PART NUMBER										
TP29095B01, CD, CT-940CH/BJO 15Ton Crimp Head										
TITLE										
CD, CT-940CH/BJO CRIMP HEAD										
CUSTOMER DRAWING										
ITEM REVISION NAME										
R29095BA/00										
DATASET FILE NAME										
R29095BA-00-dwg1										
THIRD ANGLE PROJECTION										
MATERIAL					DRAWING NUMBER					
AS NOTED					TP29095B01					
DRAWN BY		DATE		CHK		SCALE		SHEET 1 OF 1		SIZE
BJPU		7-10-18		SKB		NONE				B

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CT-940CH/BJO](#)