








THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




#10-32 THREAD FORMING SCREWS
(QTY. 6)



UGB-B-SO



#10-32 THREAD FORMING SCREWS
(QTY. 6)



UGB-IN-SO

NOTES:

1. MATERIAL:
UGB-B-SO: CDA-110 ELECTROLYTIC COPPER, TIN PLATED
UGB-IN-SO: DMC GRADE DR17 RED HARD PLASTIC
UL 94 V-0 (HALOGEN FREE)
600V OF INSULATION
2. DESIGNED FOR USE WITH PANDUIT UNIVERSAL GROUND BAR SYSTEM, UGB2/0 SERIES
3. DIMENSIONS IN BRACKETS ARE MILLIMETERS

									PANDUIT CORP.	TINLEY PARK, ILLINOIS
									UNIVERSAL GROUND BAR BONDING & ISOLATION STAND-OFFS (UGB-B-SO, UGB-IN-SO)	CUSTOMER DRAWING
									UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE:	UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
									(.X) ± (.XXX) (.XX) ± .02 [0.5]	ANGLES ±
								DRAWN BY JHNU	MAT'L:	SCALE NONE
00	1/12	JHNU	SRBI	RELEASED TO PRODUCTION	10J017CC-JC	RGB	RGB	DATE 1/12		DRAWING NO / CAD FILE DWG B SIZE
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	CHK'D SRBI		10J017CC-JC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[UGB-IN-SO](#) [UGB-B-SO](#)