



2


1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	DIM "A" INCH [mm]	DIM "B" INCH [mm]	DIM "C" INCH [mm]	DIM "D" INCH [mm]	DIM "E" REF. INCH [mm]	DIM "F" REF. INCH [mm]
SMP12A	0.79 [20.0]	0.79 [20.0]	0.21 [5.4]	0.24 [6.1]	0.55 [14.0]	0.10 [2.6]
SMP16A	1.00 [25.0]	1.00 [25.0]	0.25 [6.5]	0.30 [7.5]	0.67 [17.0]	0.13 [3.3]
SMP18A	1.18 [30.0]	1.18 [30.0]	0.28 [7.0]	0.34 [8.7]	0.79 [20.0]	0.18 [4.5]



NOTE:
SEE WWW.PANDUIT.COM FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE,
PART MATERIAL, PART COLOR AND THIRD
PARTY RECOGNITION OR COMPLIANCE.

PART NUMBER		SEE TABLE	
TITLE		STRONGHOLD MOUNTS ADHESIVE APPLIED	
CUSTOMER DRAWING			
ITEM REVISION NAME	00586EBA/01		
DATASET FILE NAME	00586EBA_DC/01A		
 THIRD ANGLE PROJECTION			
MATERIAL		DRAWING NUMBER	
NYLON 6/6		00586EBA_DC	
DRAWN BY	DATE	CHK	SCALE
JBN	02-21-20	BMAG	NONE
SHEET 1 OF 1			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
01A	07-30-20	JBN	BMAG	RGB JHAC	B. REVISED HOLE DIA TO 0.13 [3.3] WAS 0.138 [3.50] A. REVISED HOLE DIA TO 0.10 [2.6] WAS 0.114 [2.90]	076845 rev.01
00A	03-10-20	JBN	BMAG	RGB JHAC	RELEASED	076845

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[SMP12A-M](#) [SMP16A-C](#) [SMP12A-3X](#)