




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FRACTIONAL PART SIZE NOTED HERE.

"A" DIA  
WHEN CLOSED



| PANDUIT<br>PART NUMBER | "A"<br>in/(mm) | "B" REF.<br>in/(mm) | "C"<br>in/(mm) | "D"<br>in/(mm) | "E"<br>in/(mm) | WEIGHT<br>lbs (g)/ 100 pcs |
|------------------------|----------------|---------------------|----------------|----------------|----------------|----------------------------|
| CCH12-S10              | 0.12<br>(3.1)  | 0.36<br>(9.1)       | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.12 (52.5)                |
| CCH19-S10              | 0.19<br>(4.8)  | 0.42<br>(10.7)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.15 (67.2)                |
| CCH25-S10              | 0.25<br>(6.3)  | 0.46<br>(11.7)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.16 (74.0)                |
| CCH31-S10              | 0.31<br>(7.9)  | 0.50<br>(12.7)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.18 (83.7)                |
| CCH38-S10              | 0.38<br>(9.5)  | 0.53<br>(13.5)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.23 (105.8)               |
| CCH44-S10              | 0.44<br>(11.1) | 0.56<br>(14.2)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.22 (99.4)                |
| CCH50-S10              | 0.50<br>(12.7) | 0.59<br>(15.0)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.24 (109.1)               |
| CCH56-S10              | 0.56<br>(14.2) | 0.61<br>(15.5)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.25 (114.8)               |
| CCH62-S10              | 0.62<br>(15.7) | 0.65<br>(16.5)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.29 (131.1)               |
| CCH69-S10              | 0.69<br>(17.5) | 0.75<br>(19.1)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.33 (150.3)               |
| CCH75-S10              | 0.75<br>(19.1) | 0.78<br>(19.8)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.33 (149.3)               |
| CCH81-S10              | 0.81<br>(20.6) | 0.81<br>(20.6)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.34 (156.4)               |
| CCH87-S10              | 0.87<br>(22.1) | 0.84<br>(21.3)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.35 (160.9)               |
| CCH100-S10             | 1.00<br>(25.4) | 0.91<br>(23.1)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.46 (209.7)               |
| CCH112-S10             | 1.12<br>(28.4) | 0.97<br>(24.6)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.53 (239.2)               |
| CCH119-S10             | 1.19<br>(30.2) | 1.00<br>(25.4)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.57 (259.3)               |
| CCH125-S10             | 1.25<br>(31.8) | 1.06<br>(26.9)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.58 (260.8)               |
| CCH138-S10             | 1.37<br>(34.8) | 1.12<br>(28.4)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.64 (288.9)               |
| CCH150-S10             | 1.50<br>(38.1) | 1.19<br>(30.2)      | 0.050<br>(1.3) | 0.50<br>(12.7) | 0.203<br>(5.1) | 0.69 (310.9)               |

#### NOTES:

- SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

CAD FILENAME/LAYERS

G00239DW\_PI\_CCH\_02

**PANDUIT**

CORP.

TINLEY PARK, ILLINOIS

CCH - CABLE CLAMP

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:  
(.X) ±0.1(2.5) (.XXX) ±0.015(1.4)  
(.XX) ±0.05(1.3) ANGLES ±5°

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
CJG

MAT'L:

SCALE NONE

DATE

NYLON 6/6

DRAWING NO.

GB0239DW

DWG  
A  
SIZE

|     |        |     |     |                                                      |          |   |      |     |  |  |  |  |  |
|-----|--------|-----|-----|------------------------------------------------------|----------|---|------|-----|--|--|--|--|--|
| 2   | 2/7/06 | JAD |     | UPDATE LOCATION OF FRACTIONAL<br>PART SIZE INDICATOR | GB0239DW | 2 |      |     |  |  |  |  |  |
| REV | DATE   | BY  | CHK | DESCRIPTION                                          | ECN      | R | CUST | SUP |  |  |  |  |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

|                                     |                                     |                                     |                                     |                                     |                                     |                                     |
|-------------------------------------|-------------------------------------|-------------------------------------|-------------------------------------|-------------------------------------|-------------------------------------|-------------------------------------|
| <a href="#"><u>CCH12-S10-C0</u></a> | <a href="#"><u>CCH25-S10-C0</u></a> | <a href="#"><u>CCH31-S10-C0</u></a> | <a href="#"><u>CCH44-S10-C0</u></a> | <a href="#"><u>CCH50-S10-C0</u></a> | <a href="#"><u>CCH56-S10-C0</u></a> | <a href="#"><u>CCH62-S10-C0</u></a> |
| <a href="#"><u>CCH69-S10-C0</u></a> | <a href="#"><u>CCH75-S10-C0</u></a> | <a href="#"><u>CCH81-S10-C0</u></a> | <a href="#"><u>CCH87-S10-C0</u></a> | <a href="#"><u>CCH38-S10-C0</u></a> | <a href="#"><u>CCH19-S10-C0</u></a> |                                     |