

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	MATERIAL	WIDTH "A"	HEIGHT "B"	TAGS & TIES PER PKG.	LAMINATION SIDE	HEADER	HEADER COLOR	DESCRIPTION	LEGEND COLOR
PST-1	SLCT VINYL	2.00 (50.8)	3.00 (76.2)	10	FRONT ONLY	BLANK	BLANK	BLANK	BLANK
PST-2	SLCT VINYL	3.25 (82.6)	5.75 (146.0)	5	FRONT ONLY	BLANK	BLANK	BLANK	BLANK
PST-3	GMV5 AND SEZ-SNC VINYL	3.00 (76.2)	5.75 (146.0)	5	FRONT ONLY	DANGER	WHITE/RED & BLACK	SEE NOTE 2	BLACK/WHITE
PST-4	GMV5 AND SEZ-SNC VINYL	3.50 (88.9)	5.75 (146.0)	25	FRONT ONLY	BLANK	BLANK	BLANK	BLANK
PST-5	GMV5 AND SEZ-SNC VINYL	3.50 (88.9)	5.75 (146.0)	25	FRONT AND BACK	BLANK	BLANK	BLANK	BLANK
PST-12	GMV5 AND SEZ-SNC VINYL	3.00 (76.2)	5.75 (146.0)	5	FRONT ONLY	BLANK	BLANK	DO NOT THROW SYMBOL (SEE NOTE 3)	BLACK/WHITE

NOTES:

1. MILLIMETER ARE IN ().

NOTE 2



NOTE 3



Front PST-3 Back



Front PST-12 Back



										CAD FILENAME/LAYERS		I00318LX_DC_C10679/00A			
										PANDUIT CORP. TINLEY PARK, ILLINOIS CUSTOMER DRAWING PST-* INDOOR RIGID VINYL SAFETY TAG CARRIER AND PHOTO TAGS					
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .075 (.XXX) ± .020 (.XX) ± .050 ANGLES ± 5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
										DRAWN BY RVU	MAT'L: SEE TABLE		SCALE NTS		
O	4/4/08	RVU		DRAWING RELEASE.	5382	R				DATE 4/4/08			DRAWING NO.		DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		CHK'D			C10679		SIZE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

PST-1