

Technical drawing of a duct assembly, showing three views: a top view (top), a side view (left), and a front view (bottom).

Top View Dimensions:

- Overall width: 4.14 [105.2]
- Overall height: 4.25 [108.0]
- Top flange thickness: .195 TYP [5.0]
- Top flange width: .50 TYP [12.6]
- Internal vertical spacing: 1.50 TYP [38.1]
- Internal horizontal spacing: 2.00 [50.8] and 4.00 TYP [101.6]

Side View Dimensions:

- Overall height: 5.06 [128.5]
- Internal height: 5.00 [127.0]
- Top flange thickness: .09 [2.3]

Front View Dimensions:

- Overall width: 4.25 [108.0]
- Internal width: 1.33 TYP [33.9]
- Bottom flange thickness: .38 TYP [9.5]

Callouts:

- COVER - - PART NUMBER NC4**6
- DUCT - - PART NUMBER NE4X5**6

4	1-13-10	JCST	MKBE	J. REDRAWN - THICKNESS AND HEIGHT DIMENSIONS CHANGED
3	10-01-08	JCST	MKBE	I. MODIFIED NOTES H. CHANGED MATERIAL
--	-----	---	----	G. ADDED LENGTH NOTE F. CORRECTED DIMENSION
2	8-7-07	JCST	MKBE	E. DELETED DIMENSION D. ADDED DIMENSION
1	9-9-05	JCST	MKBE	B. CHANGED TITLE BLOCK C. CHANGED VIEWS A. ADDED LABELS, AND NOTES
R	10-16-03	JHNU	JGG	DRAWING RELEASED
REV	DATE	BY	CHK	DESCRIPTION

CAD FILENAME/LAYERS		D11000SF_DC/03A	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
WIRING DUCT - TYPE NE WITH COVER			
4 X 5			
MARKETING DRAWING			
DRAWN BY JHNU	MAT'L:	SCALE	FULL
DATE 10-16-03	HALOGEN FREE MODIFIED PPO	DRAWING NO.	DWG C
CHECKED BY JGG		36897-959	SIZE

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[NE4X5WH6](#)