


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER*	LOOP DIAMETER		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs (N)	TIP STYLE	WEIGHT lbs / 100 (g) / PCS.	GS4H TOOL SETTING
	FIXED in (mm)	ADJUSTABLE in (mm)										
DHC1.12X 1.75	1.12 (28.4)	1.0 TO 1.75 (25.4 TO 44.45)	.050 (1.3)	.280 (7.1)	.23 (5.8)	.31 (7.9)	.44 (11.2)	11.0 (279)	100 (445)	CURVED	.75 (340)	4

NOTES:

- * 1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 2. COLOR: BLACK

2. COLOR: BLACK										CAD FILENAME/LAYERS	
										DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS	
										PANDUIT CORP. TINLEY PARK, ILLINOIS	
										DOUBLE HOSE CLAMP-DHC1.12 X 1.75	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.1 (2.5) (.XXX) ± (.XX) ±.02(.51) ANGLES ±	
										UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
										DRAWN BY KET	MAT'L: NYLON 6/6 WEATHER RESISTANT
5	12/23/03	JABO		CORRECTED METRIC CONVERSION OF ADJ. LOOP DIA			SS-6483	5		DATE 6/2/95	SCALE NONE
REV	DATE	BY	CHK	DESCRIPTION			ECN	-	R	CUST	SUP
										CHK'D HVP	DWG SIZE A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[DHC1.12X1.75-D0](#)