



PANDUIT PART NO.	"A"	"B"	WEIGHT lbs. / 100 (g) / pcs.
MP250W175	2.50 (63.5)	2.03 (51.6)	.25 (113.5)



NOTES:
*1. SEE CURRENT PRICE SHEET FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.

I	8/3/01	LGG		ADDED REF AND UPDATED	GB0239GM	I		
R	1-10-00	JAD		INITIAL RELEASE, REPLACES SS-462B REV 4	GB0239GM	R		
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	

DIMENSIONS IN BRACKETS ARE METRIC [mm]			
CAD FILENAME/LAYERS G00239GN_PB_MP250W175_01			
 CORP. TINLEY PARK, ILLINOIS			
IDENTIFICATION MARKER PLATE			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25] (.XX) ±0.02 [0.5] ANGLES ±5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY JAD	MAT'L: WHITE NYLON 6/6	SCALE NONE	
DATE 1/10/2000		DRAWING NO. GB0239GN	DWG A SIZE
CHK'D			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[MP250W175-C](#) [MP250W175-M](#)