







DUST PLUGS NOT SHOWN FOR CLARITY



NOTES:

- SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- MATERIALS:
 - PLATE: C.R.S. POWDER COATED.
 - ADAPTER: COMPOSITE WITH METAL CLIP.
 - ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
- ADAPTERS ARE SUPPLIED WITH TWO DUST PLUGS.
- DIMENSIONS IN BRACKETS ARE METRIC.
- WHITE MARK ON MPO ADAPTER CORRELATES TO FIRST FIBER ON INSTALLED MPO/MTP CONNECTOR.



											8 POSITION HORIZONTAL MPO FIBER ADAPTER PANEL CUSTOMER DRAWING			
														
												ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.		
												DRAWING FILENAME M01945XY_DC/00A		
												SCALE NONE		
											 THIRD ANGLE PROJECTION	DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES		
												PART NO. FAPH0812BLMPO FAPH0812CGMPO		
												DRAWING NO. 01945-157		
												SIZE A		
R	03-07-11	MC		RELEASED TO PRODUCTION		01945-157					DRAWN BY MC	REVIEW DRAWING NUMBERS		
											DATE 02-28-11			
REV	DATE	BY	CHK	DESCRIPTION		ECN - R		CUST	SUP	OTH	CHK'D			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[FAPH0812BLMPO](#)