


2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	PACKAGE QTY.	MAX BUNDLE DIA	"LENGTH" ±.3 [7]
MLTFC2H-LP316	50	2" [51]	7.9"[201]
MLTFC2.7H-LP316	50	2.7" [69]	10.15"[258]
MLTFC4H-LP316	50	4" [102]	14.3"[362]
MLTFC6H-LP316	50	6" [152]	20.5"[521]
MLTFC8H-LP316	50	8" [203]	26.8"[679]

B



NOTES:

1. APPLICATION TOOLS - GS4MT, PPTMT, ST2MT, HTMT OR ST3MT
2. MINIMUM LOOP TENSILE STRENGTH - 250 LBS. (1112 NEWTONS)
WHEN TESTED ON A 1.5" MANDREL.
3. BRACKETS [] DENOTE DIMENSIONS IN MILLIMETERS, AND ARE SHOWN FOR REFERENCE ONLY
4. TOLERANCES:
.XXX = ±.010 [.25] .XX = ±.02 [.5]
.X = ±.03 [.8] ANGLES = ±2°
5. MATERIAL: 316 STAINLESS STEEL
6. COATING - POLYESTER
COATING THICKNESS: .002 MIN./ .005 MAX. PER SIDE

FULLY ROUNDED
EDGES ALONG
STRAP BODY

SECTION A - A
SCALE 4:1

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
04A	4/13	JAMB	MIM	RGRO	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01047
03A	2/12	MIM	RGRO	---	NOTE #3 METRIC DIMENSIONS NOTED AS BEING SHOWN FOR REFERENCE ONLY	-----
02	11/05	JMMR	EJD	---	ADDED MLTFC2.7H-LP316 TO TABLE	SS00112
01	3/05	JAMB	PAB	JJJ	DRAWING REVISED TO REFLECT CURRENT COATED HEAVY SERIES PRODUCT	12501
00	11/04	JAMB	PAB	JJJ	DRAWING RELEASED	12169

TITLE					
METAL LOCKING TIE - COATED HEAVY SERIES					
CUSTOMER DRAWING					
ITEM REVISION NAME			N41193BS/04		
DATASET FILE NAME			N41193BS/04		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			PANDUIT MATERIAL: 316 STAINLESS STEEL		
.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					
THIRD ANGLE PROJECTION			DRAWING NUMBER: N41193BS_DC		
DRAWN BY	DATE	CHK	SCALE	SIZE	
JAMB	11/04	PAB	2:1	A	

A

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[MLTFC6H-LP316](#) [MLTFC2.7H-LP316](#)