


PART NO.	"A" (IN.) MIN.	"B" (IN.) ±0.062	"C" +/- .062 (IN.)	MATERIAL	COLOR	PART NO.	"A" (IN.) MIN.	"B" (IN.) ±.062	"C" +/- .062 (IN.)	MATERIAL	COLOR
T100X000YK1	1200	1.00	0.125	GMV4-C	CLEAR	T200X000VSIY	1200	2.00	0.125	GMV14	GREEN
T200X000VRIY	1200	2.00	0.125	GMV14	BROWN	T200X000VUIY	1200	2.00	0.125	GMV14	ORANGE
T200X000YK1	1200	2.00	0.125	GMV4-C	CLEAR	T200X000VWIY	1200	2.00	0.125	GMV14	RED
T225X000YK1	1200	2.25	0.125	GMV4-C	CLEAR	T200X000VXIY	1200	2.00	0.125	GMV14	YELLOW
T400X000VRIY	1200	4.00	0.125	GMV14	BROWN	T400X000VYIY	1200	4.00	0.125	GMV15	BLACK
T400X000YK1	1200	4.00	0.125	GMV4-C	CLEAR	T400X000VTIY	1200	4.00	0.125	GMV14	GRAY
T425X000YK1	1200	4.25	0.125	GMV4-C	CLEAR	T400X000VVIY	1200	4.00	0.125	GMV15	PURPLE
T100X000VPIY	1200	1.00	0.125	GMV14	WHITE	T400X000VPIY	1200	4.00	0.125	GMV14	WHITE
T100X000VUIY	1200	1.00	0.125	GMV14	ORANGE	T400X000VQIY	1200	4.00	0.125	GMV15	BLUE
T100X000VXIY	1200	1.00	0.125	GMV14	YELLOW	T400X000VSIY	1200	4.00	0.125	GMV14	GREEN
T100X000VQIY	1200	1.00	0.125	GMV15	BLUE	T400X000VUIY	1200	4.00	0.125	GMV14	ORANGE
T100X000VSIY	1200	1.00	0.125	GMV14	GREEN	T400X000VWIY	1200	4.00	0.125	GMV14	RED
T100X000VWIY	1200	1.00	0.125	GMV14	RED	T400X000VXIY	1200	4.00	0.125	GMV14	YELLOW
T100X000VYIY	1200	1.00	0.125	GMV15	BLACK	T200X000Y2T	180	2.00	0.125	GMV4-HT	WHITE/GREEN
T200X000VYIY	1200	2.00	0.125	GMV15	BLACK	T400X000Y2T	180	4.00	0.125	GMV4-HT	WHITE/GREEN
T200X000VTIY	1200	2.00	0.125	GMV14	GRAY						
T200X000VVIY	1200	2.00	0.125	GMV15	PURPLE						
T200X000VPIY	1200	2.00	0.125	GMV14	WHITE						
T200X000VQIY	1200	2.00	0.125	GMV15	BLUE						



NOTES:
1. RESIN RIBBON
RECOMMENDED.

CAD FILENAME/LAYERS

100472ER-DC-C10274/11H

PANDUIT CORP. TINLEY PARK, ILLINOIS

THERMAL TRANSFER CONTINUOUS TAPES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .12 (XXX) ± .025
(.XX) ± .062 ANGLES ±

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

7	6/21/12	RVU		CHANGE GMV15 INSTEAD OF GMV14 (for the black and purple parts only).	GAECN00035	R				DRAWN BY RVU	MAT'L:	SCALE NTS
6	5/7/12	RVU		GMV14 CHANGES TO GMV15.	6778	R				DATE 10-25-06	SEE TABLE	DRAWING NO. C10274
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D		DWG SIZE A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[T400X000YK1](#) [T100X000VP1Y](#) [T225X000YK1](#) [T400X000VQ1Y](#) [T100X000VY1Y](#) [T200X000YK1](#) [T200X000VT1Y](#)
[T100X000VS1Y](#) [T100X000VW1Y](#) [T400X000VR1Y](#) [T200X000VV1Y](#)