



Part Number: PBC200CD4B

Product Description: SCREW-ON BEAM CLAMP FOR UP TO 1/2" FLANGE WITH 1-1/2" RIGID / IMC CONDUIT CLIP

**Material Specifications**

Type: Assembly

Finish: Assembly

Color: Various

Function Specifications**Compatible Wires and Cables**

AC/MC CABLE (OD):

Drop Wire:

Plain Rod (in):

Threaded Rods and Bolts

Tapped Holes: 1/4-20 on back of clamp

Clearance Holes (in):

Threaded Rod Size (in):

Compatible Conduit

EMT Size (in):

Rigid/IMC (in): 1-1/2

Compatible Flanges and Studs

Flange Size (in): Up to 1/2

Metal Stud Size (ins):

Static Load Rating

Vertical (lbs):

Horizontal (lbs):

Other

1/4-20 Bolt and nut included to secure conduit

Codes and RegulatoryRegulatory
Certifications: -

Country of Origin: US

Packaging

General Packaging: Cardboard Box

Box Size: 15 X 8.25 X 7.25

Pieces per Package: 50

Other Box Features:

Document Information

Created By: DBLA

Checked By: DJW

Approved By: KLN

Customer Specification #: C11134

Revision Level: 01

ECN #: GAECN01482

Date: 12/10/2013

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PBC200CD4B](#)