



Part Number: PM24

Product Description: BEAM CLAMP FOR 1/8" - 1/4" FLANGE

**Material Specifications**

Type: High Carbon Steel, Spring Tempered

Finish: Zinc Phosphate and Oil

Color: Black

Function Specifications**Compatible Wires and Cables**

AC/MC CABLE (OD):

Drop Wire:

Plain Rod (in):

Threaded Rods and Bolts

Tapped Holes: 1/4-20 on back and bottom of clamp

Clearance Holes (in): 1/4 star hole

Threaded Rod Size (in):

Compatible Conduit

EMT Size (in):

Rigid/IMC (in):

Compatible Flanges and Studs

Flange Size (in): 1/8 to 1/4

Metal Stud Size (ins):

Static Load Rating

Vertical (lbs): 75 or 100

Horizontal (lbs):

Other

Max load depends on load location

Codes and RegulatoryRegulatory
Certifications: UL/cUL

Country of Origin: US

--

--

Packaging

General Packaging: Cardboard Box

Box Size: 8.25 X 7.25 X 5.75

Pieces per Package: 100

Other Box Features:

Document Information

Created By: DBLA

Checked By: DJW

Approved By: KLN

Customer Specification #: C11147

Revision Level: 01

ECN #: GAECN01482

Date: 12/10/2013

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PM24](#)