

Part Number:	PSCH64B
Product Description:	ONE-PIECE STRUT CLAMP WITH SADDLE USED TO SECURE 3-1/2" CONDUIT



Material Specifications

Type:	Zinc Plated Steel	Finish:	Zinc
Color:	Silver		

Function Specifications

Compatible Wires and Cables

AC/MC CABLE (OD):	
Drop Wire:	
Plain Rod (in):	

Threaded Rods and Bolts

Tapped Holes:	
Clearance Holes (in):	
Threaded Rod Size (in):	

Compatible Conduit

EMT Size (in):	3-1/2
Rigid/IMC (in):	3-1/2

Compatible Flanges and Studs

Flange Size (in):	
Metal Stud Size (ins):	

Static Load Rating

Vertical (lbs):	200
Horizontal (lbs):	

Other

Clamps with Saddle, suitable for use with standard 1-5/8 strut
--

Codes and Regulatory

Regulatory Certifications:	UL/cUL	Country of Origin:	CN
----------------------------	--------	--------------------	----

Packaging

General Packaging:	Cardboard Box	Pieces per Package:	10
Box Size:	8.25 X 6.25 X 6	Other Box Features:	

Document Information

Created By:	DBLA	Customer Specification #:	C11394
Checked By:	DJW	Revision Level:	01
Approved By:	KLN	ECN #:	GAECN01482
		Date:	12/10/2013

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PSCH64B](#)