

Part Number:	PSCH56B
Product Description:	ONE-PIECE STRUT CLAMP WITH SADDLE USED TO SECURE 3" CONDUIT



Material Specifications

Type:	Zinc Plated Steel	Finish:	Zinc
Color:	Silver		

Function Specifications

Compatible Wires and Cables		Threaded Rods and Bolts	
AC/MC CABLE (OD):		Tapped Holes:	
Drop Wire:		Clearance Holes (in):	
Plain Rod (in):		Threaded Rod Size (in):	
Compatible Conduit		Compatible Flanges and Studs	
EMT Size (in):	3	Flange Size (in):	
Rigid/IMC (in):	3	Metal Stud Size (ins):	
Static Load Rating		Other	
Vertical (lbs):	160	Clamps with Saddle, suitable for use with standard 1-5/8 strut	
Horizontal (lbs):			

Codes and Regulatory

Regulatory Certifications:	UL/cUL	Country of Origin:	CN
----------------------------	--------	--------------------	----

Packaging

General Packaging:	Cardboard Box	Pieces per Package:	10
Box Size:	8.25 X 6.25 X 6	Other Box Features:	

Document Information

Created By:	DBLA	Customer Specification #:	C11393
Checked By:	DJW	Revision Level:	01
Approved By:	KLN	ECN #:	GAECN01482
		Date:	12/10/2013

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PSCH56B](#)