

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS - IN.					TOOL
		A±.03	W±.01	C±.02	M±.03	H±.01	
PK6-8R	#8	1.59 (40.39)	.47 (11.94)	.43 (10.92)	1.36 (34.54)	.18 (4.57)	CT-2600 WITH DIE # CD-2600-PV6
PK6-10R	#10	1.60 (40.64)	.47 (11.94)	.43 (10.92)	1.36 (34.54)	.20 (5.08)	
PK6-14R	1/4"	1.63 (41.40)	.47 (11.94)	.48 (12.19)	1.36 (34.54)	.27 (6.86)	
PK6-56R	5/16"	1.72 (43.69)	.62 (15.75)	.53 (13.46)	1.42 (36.07)	.33 (8.38)	
PK6-38R	3/8"	1.72 (43.69)	.62 (15.75)	.51 (12.95)	1.42 (36.07)	.40 (10.16)	
PK6-12R	1/2"	1.82 (46.23)	.82 (20.83)	.51 (12.95)	1.42 (36.07)	.52 (13.21)	

NOTES:

- RATED FOR:
A. #6 AWG STRANDED COPPER WIRE
- SEE www.panduit.com FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.
- MATERIAL:
A. STAMPING - .045" (1.14) THK COPPER,
TIN PLATED
B. HOUSING - KYNAR, BLUE STRIPE
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
- WIRE STRIP LENGTH: 7/16" +1/32" (11.1 +0.8)
-0 -0.0



LISTED
587H
E52164



TITLE
#6 BARREL KYNAR INSULATED RING TONGUE
.360 (9.14) MAX. WIRE INSUL. DIAMETER

CUSTOMER DRAWING

ITEM REVISION NAME

N41715BA/04


DATASET FILE NAME

N41715BA/04

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN (mm)

.X ±
.XX ±

.XXX ±
ANGLES ±



THIRD ANGLE
PROJECTION

MATERIAL:

SEE NOTES

DRAWING NUMBER:

A41715

DRAWN BY

DATE

JHNU 2/05

CHK

LCA

SCALE

N/A

SHT 1 OF 1

SIZE

A

04	5/14	JHNU	JHNU	RGB	REVISED TABLE: ADDED TOOL INFORMATION ADDED UL LOGO REVISED TITLE BLOCK	N41715BA- A41715
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[PK6-8R-T](#)