


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS in.				
		A $\pm .03$	W $\pm .01$	C $\pm .02$	M $\pm .03$	H $\pm .01$
P6-8RHT6-E	#8	1.21 (30.73)	.47 (11.94)	.43 (10.92)	.97 (24.64)	.17 (4.32)
P6-10RHT6-E	#10	1.21 (30.73)	.47 (11.94)	.43 (10.92)	.97 (24.64)	.20 (5.08)
P6-10RHT6-T	#10	1.21 (30.73)	.47 (11.94)	.43 (10.92)	.97 (24.64)	.20 (5.08)
P6-14RHT6-E	1/4"	1.21 (30.73)	.47 (11.94)	.43 (10.92)	.97 (24.64)	.27 (6.86)
P6-56RHT6-E	5/16"	1.33 (33.78)	.62 (15.75)	.51 (12.95)	1.02 (25.91)	.33 (8.38)
P6-38RHT6-E	3/8"	1.33 (33.78)	.62 (15.75)	.51 (12.95)	1.02 (25.91)	.39 (9.91)
P6-12RHT6-E	1/2"	1.43 (36.32)	.82 (20.83)	.51 (12.95)	1.02 (25.91)	.52 (13.21)

NOTES:

1. FOR #6 AWG STRANDED COPPER WIRE
2. 650° F (343° C) MAX OPERATING TEMP
3. PACKAGE QTY: STD. PKG. -E=20
BULK PKG. -T=200
4. MATERIAL: .045" (1.14) THK COPPER, NICKEL PLATED
5. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
6. INSTALLATION TOOL: CT-2600
7. WIRE STRIP LENGTH: 7/16 ^{+1/32}₋₀ (11.1 ⁺⁸₋₀)



								 PANDUIT CORP. TINLEY PARK, ILLINOIS			
								#6 BARREL NON-INSULATED RING TONGUE			
00	6/08	BCT		RELEASED							
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY BCT	CHK'D	SCALE NONE	DRAWING NO. A41742

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[P6-10RHT6-E](#) [P6-12RHT6-E](#) [P6-38RHT6-E](#) [P6-56RHT6-E](#) [P6-8RHT6-E](#) [P6-14RHT6-E](#)