





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PART NUMBER		CBXC4** - A		PRODUCT SPEC/PKG SPEC		N/A	
I.I. NUMBER		N/A		WORK INSTRUCTION		N/A	
TITLE							
MINICOM LOW PROFILE 4 PORT SURFACE MOUNT BOX							
CUSTOMER DRAWING							
ITEM REVISION NAME				M00056BE/04.PRT			
DATASET FILE NAME				M00056BE_DC/04B.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]				<div>MATERIAL :</div> <div>ABS</div> <div>DRAWING NUMBER:</div> <div>00056-03</div>			
<div><div><div>.X ±</div><div>.XX ± .03 [ .8 ]</div></div><div><div>.XXX ± .010 [ .3 ]</div><div>ANGLES ±</div></div></div> <div><div></div><div>THIRD ANGLE PROJECTION</div></div>							
DRAWN BY		DATE		CHK		SCALE	
JSP		9-9-98		PBD		NONE	
SHT 2 OF 2						SIZE	
						A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	7-01-13	MDJR	JSP	JSP	SEE SHEET 1 OF 2.	00056-03
2	11-14-12	BJN	JSP	JSP	SEE SHEET 1 OF 2	00056-03
1	11-17-98	JSP	PBD	CYM	SEE SHEET 1 OF 2	00056-03
R	9-9-98	JSP	PBD	RJD	SEE SHEET 1 OF 2	00056-03

2

1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
CBXC4**-A	.79 LB/10 PCS (359.5 g/10 PCS)



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. OPTIONAL MAGNET (CBM-X) ADHERES TO BOX BASE IN TWO LOCATIONS FOR MOUNTING ON METAL SURFACES.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. BREAKOUTS DESIGNED TO ACCEPT LD3 AND LD5 RACEWAYS.
6. LOW PROFILE BOX HOLDS UP TO 4 MINI-COM MODULES.
7. ALSO INCLUDED WITH BOX:
  - a. (1) PLT1.51-C PAN-TY
  - b. (2) STRIPS OF 1.25" X .75" 32W125X75STR FOAM TAPE FOR MOUNTING. (BASE CONTAINS TAPE LOCATION INDICATORS.)

NO WARRANTY, EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

PART NUMBER	CBXC4**-A	PRODUCT SPEC/PKG SPEC	N/A
I.I. NUMBER	N/A	WORK INSTRUCTION	N/A
TITLE			
MINICOM LOW PROFILE 4 PORT SURFACE MOUNT BOX			
CUSTOMER DRAWING			
ITEM REVISION NAME	M00056BE/04.PRT		
DATASET FILE NAME	M00056BE_DC/04B.PRT		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]			MATERIAL:
.X ± .XX ± .03 [ .8 ]			ABS
.XXX ± .010 [ .3 ]			DRAWING NUMBER:
ANGLES ±			00056-03
THIRD ANGLE PROJECTION			
DRAWN BY	DATE	CHK	SCALE
JSP	9-9-98	PBD	NONE
SHT 1 OF 2			SIZE
			A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	7-01-13	MDJR	JSP	JSP	C. CHANGED TITLE TO MINICOM AND ADDED "4 PORT".	
2	11-14-12	BJN	JSP	JSP	B. UPDATED DRAWING FORMAT TO REFLECT CURRENT LOGO	00056-03
1	11-17-98	JSP	PBD	CYM	A. WEIGHT WAS .32#/10PCS.	00056-03
R	9-9-98	JSP	PBD	FJD	RELEASED TO PRODUCTION	00056-03

2

1

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CBXC4WH-A](#) [CBXC4IG-A](#) [CBXC4EI-A](#) [CBXC4IW-A](#) [CBXC4BL-A](#)