


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
CFG2**	.23 LB/10 PCS (106 g/10 PCS)


NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. (2) #6-32 X 1" PANHEAD SCREWS ARE SUPPLIED



LATCHING HOOKS
FOR PANDUIT
MODULES



PART NUMBER CFG2**		PRODUCT SPEC/PKG SPEC N/A	
I.I. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE "GFCI" MODULE FRAME TWO POSITION			
CUSTOMER DRAWING			
ITEM REVISION NAME M00021CA/02.PRT		PANDUIT TM	
DATASET FILE NAME M00021CA_DC04/02A.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [0.127] .xx ± .01 [0.25] ANGLES ± 5 °		MATERIAL : ABS	
		DRAWING NUMBER: 00021 - 04	
DRAWN BY RCA	DATE 7-28-97	CHK CEF	SCALE NONE
REV		SIZE A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
4	11-6-12	BJN	JSP	JSP	A. UPDATED FORMAT TO REFLECT CURRENT PANDUIT LOGO REVISED & REDRAWN PREVIOUS REVS REMOVED FOR CLARITY	00021-04

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CFG2BL](#) [CFG2IW](#) [CFG2WH](#) [CFG2IG](#) [CFG2EI](#)