

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FIGURE 1
DP6 PLUS 48 PORT PATCH PANEL

PANDUIT P/N	WEIGHT (APPROX.)
DPKR48688TG	2.40 LB (1088.6 g)

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AS WELL AS OPTIONAL ICONS.
- KIT INCLUDES THE FOLLOWING:
 - 1 - LABEL SET 1-24
 - 1 - LABEL SET 25-48
 - 1 - BLANK LABEL
 - 9 - LABEL HOLDERS
 - 1 - STRAIN RELIEF BAR
 - 1 - DP6 PLUS 48 PORT PATCH PANEL
 - 8 - 12-24 X 1/2" ROUND HEAD SCREWS
- MATERIAL:
 - PANEL HOUSING: STEEL
 - RJ45 MODULE: THERMOPLASTIC RESIN UL94V-0
 - PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
 - BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
 - RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
 - STRAIN RELIEF BAR: STEEL BAR STOCK
 - LABEL: VINYL
 - LABEL HOLDER: CLEAR VINYL
- 48 PORT PATCH PANEL 8 POSITION 8 WIRE.
- THE PATCH PANEL AND STRAIN RELIEF BAR ARE DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- USE 110 STYLE TERMINATION TOOL FOR PUNCHDOWN.
- RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.


PART NUMBER		DPKR48688TG	
TITLE			
DP6 PLUS 48 PORT PATCH PANEL WITH STRAIN RELIEF BAR AND LABEL KIT			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01537E0/02	
DATASET FILE NAME		M01537E0_DC54/02A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XXX ± .010 [.3]		SEE NOTE 3	
.XX ± .03 [.8]		DRAWING NUMBER:	
ANGLES ±		01537-54	
THIRD ANGLE PROJECTION		SIZE	
DRAWN BY		DATE	
BJN		11/26/07	
CHK		SCALE	
RJDU		NONE	
SHT 1 OF 2		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	11/15/18	BAME	KRKE	MMR	B. REMOVED METRIC MOUNTING SCREWS	01537-54
1	6/02/14	MDJR	REFR	MMR	A. UPDATED TITLE BLOCKS.	01537-54
R	11/26/07	BJN	RJDU	VMB	RELEASED TO PRODUCTION	01537-54


2

1




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



LABEL SET 1 - 24



LABEL SET 25 - 48

LABEL HOLDER
FIGURE 2
LABEL KITFIGURE 3
STRAIN RELIEF BAR

PART NUMBER

DPKR48688TG

TITLE

DP6 PLUS 48 PORT PATCH PANEL WITH STRAIN RELIEF
BAR AND LABEL KIT


CUSTOMER DRAWING

ITEM REVISION NAME

M01537E0/02

DATASET FILE NAME

M01537E0_DC54/02A

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm].X ±
.XX ± .03 [.8].XXX ± .010 [.3]
ANGLES ±THIRD ANGLE
PROJECTION

MATERIAL:

SEE NOTE 3 ON SHEET 1

DRAWING NUMBER:

01537-54

DRAWN BY

BJN

DATE

11/26/07

CHK

RJDU

SCALE

NONE

SHT 2 OF 2

SIZE

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	11/15/18	BAME	KRKE	MME	SEE SHEET 1 OF 2 FOR CHANGES.	01537-54
1	6/02/14	MDJR	REFR	MMR	SEE SHEET 1 OF 2 FOR CHANGES.	01537-54
R	11/26/07	BJN	RJDU	VMB	SEE SHEET 1 OF 2 FOR CHANGES.	01537-54

2

1

D10100DA/14

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[DPKR48688TG](#)