


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- ** 1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
 2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
 3. TERMINATED WITH (8 POSITION) SHIELDED MODULAR PLUGS ON BOTH ENDS PER T568A.
 4. CONSTRUCTED WITH 26AWG STRANDED CAT5e F/UTP LSZH/CM PATCH CABLE. CABLE COLOR: INTERNATIONAL GRAY
 5. MATERIAL:
 PLUG: POLYCARBONATE
 SHIELD: COPPER ALLOY NICKEL PLATED
 BOOT: THERMOPLASTIC RESIN
 CABLE: DUAL-RATED CM/LSZH
 6. NOMINAL CABLE JACKET DIAMETER IS 0.205 IN (5.21MM).



T568A WIRING SCHEME

PLUG POSITION:	CABLE WIRE:
1	WHITE/GREEN
2	GREEN
3	WHITE/ORANGE
4	BLUE
5	WHITE/BLUE
6	ORANGE
7	WHITE/BROWN
8	BROWN

SEE SHEET 2 FOR PATCH CORD LENGTHS AND PART NUMBERS

PART NUMBER		STPCHAAMB**	
TITLE		TX5e SHIELDED PATCH CORDS (CM/LSZH)	
CUSTOMER DRAWING			
ITEM REVISION NAME		M01895CB/00	
DATASET FILE NAME		M01895CB_DC07/00G	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.X ± .XX ±		.XXX ± ANGLES ±	
THIRD ANGLE PROJECTION		SEE NOTES	
DRAWN BY BJN		DATE 6-4-06	
CHK EJH		SCALE NONE	
DRAWING NUMBER: 01895-07		SHT 1 OF 1	
SIZE A			


REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
6	4-12-16	BJN	MDJR	SASK	Q. REMOVED BROWN COLOR FROM PRODUCT OFFERING P. UPDATED TITLE BLOCK REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	01895-07

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

TX5e SHIELDED PATCH CORDS

PART NUMBER	LENGTH(MIN) ft(m)
STPCH0.5MB**	1.64ft (0.5m)
STPCH1MB**	3.28ft (1m)
STPCH1.5MB**	4.92ft (1.5m)
STPCH2MB**	6.56ft (2m)
STPCH2.5MB**	8.20ft (2.5m)
STPCH3MB**	9.84ft (3m)
STPCH4MB**	13.12ft (4m)
STPCH5MB**	16.40ft (5m)
STPCH6MB**	19.68ft (6m)
STPCH7MB**	22.97ft (7m)
STPCH8MB**	26.25ft (8m)
STPCH9MB**	29.53ft (9m)
STPCH10MB**	32.80ft (10m)
STPCH15MB**	49.21ft (15m)
STPCH20MB**	65.62ft (20m)
STPCH25MB**	82.02ft (25m)
STPCH30MB**	98.42ft (30m)
STPCH35MB**	114.83ft (35m)
STPCH40MB**	131.23ft (40m)

BOOT COLORS	** = COLOR
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR



CROSS-SECTIONAL VIEW OF CABLE

PART NUMBER		STPCHAAMB**	
TITLE			
TX5e SHIELDED PATCH CORDS (CM/LSZH)			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01895CB/00	
DATASET FILE NAME		M01895CB_DC07/00G	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		PANDUIT MATERIAL: SEE NOTES	
.X ± .XXX ± .XX ± ANGLES ±			
THIRD ANGLE PROJECTION		DRAWING NUMBER:	
		01895-07	
DRAWN BY	DATE	CHK	SCALE
BJN	6-4-06	EJH	NONE
SHT 2 OF 2			SIZE
			A

6	4-12-16	BJN	MDJR	SASK	SEE SHEET 1 FOR REVISION HISTORY	01895-07
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[STPCH1.5MBBL](#) [STPCH25MBBU](#) [STPCH1MBBL](#) [STPCH3MBBL](#) [STPCH1MBGR](#) [STPCH10MBRD](#)
[STPCH0.5MBBL](#) [STPCH10MBBL](#) [STPCH5MBBL](#) [STPCH2MBBL](#) [STPCH4MBBL](#) [STPCH7MBRD](#) [STPCH4MBRD](#)
[STPCH30MBBU](#) [STPCH30MBGR](#) [STPCH18MBRD](#) [STPCH14MBYL](#) [STPCH40MBGR](#) [STPCH0.5MBGR](#)
[STPCH3.5MBGR](#) [STPCH4MBGR](#) [STPCH11MBGR](#) [STPCH7MBGR](#) [STPCH28MBYL](#) [STPCH0.5MBRD](#)
[STPCH40MBBL](#) [STPCH6MBYL](#) [STPCH1.5MBRD](#) [STPCH4.5MBBU](#) [STPCH20MBBL](#) [STPCH27MBGR](#)
[STPCH18MBBL](#) [STPCH13MBBL](#) [STPCH21MBBR](#) [STPCH17MBBU](#) [STPCH8MBYL](#) [STPCH14MBRD](#)
[STPCH4.5MBGR](#) [STPCH12MBBL](#) [STPCH26MBBL](#) [STPCH16MBYL](#) [STPCH8MBBL](#) [STPCH11MBBU](#)
[STPCH11MBBL](#) [STPCH14MBBU](#) [STPCH16MBGR](#) [STPCH33MBBR](#) [STPCH15MBYL](#) [STPCH23MBYL](#)
[STPCH28MBBR](#) [STPCH17MBYL](#) [STPCH19MBRD](#) [STPCH2MBRD](#) [STPCH20MBRD](#) [STPCH23MBGR](#)
[STPCH34MBBU](#) [STPCH9MBBU](#) [STPCH10MBBU](#) [STPCH32MBRD](#) [STPCH28MBBU](#) [STPCH30MBYL](#)
[STPCH22MBBR](#) [STPCH2.5MBGR](#) [STPCH2.5MBBL](#) [STPCH27MBBR](#) [STPCH25MBYL](#) [STPCH4MBBU](#)
[STPCH5MBRD](#) [STPCH32MBBL](#) [STPCH2.5MBYL](#) [STPCH31MBGR](#) [STPCH35MBBL](#) [STPCH2MBYL](#)
[STPCH35MBGR](#) [STPCH33MBRD](#) [STPCH16MBBR](#) [STPCH26MBGR](#) [STPCH19MBYL](#) [STPCH4.5MBRD](#)
[STPCH27MBBU](#) [STPCH17MBGR](#) [STPCH27MBYL](#) [STPCH3MBBU](#) [STPCH13MBRD](#) [STPCH18MBGR](#)
[STPCH9MBRD](#) [STPCH0.5MBYL](#) [STPCH23MBBU](#) [STPCH6MBBU](#) [STPCH29MBBU](#) [STPCH15MBGR](#)
[STPCH27MBRD](#) [STPCH12MBGR](#) [STPCH3.5MBBL](#) [STPCH2.5MBRD](#) [STPCH15MBRD](#) [STPCH19MBGR](#)
[STPCH31MBBL](#) [STPCH29MBYL](#) [STPCH18MBBR](#)