


2

1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	BUNDLE DIA.		A in. (mm)	B in. (mm)	C in. (mm)	D in. (mm)	E in. (mm)	F in. (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs. (g) / 100 pcs.
	MIN. in. (mm)	MAX. in. (mm)										
PLWS2EH	0.38 (9.5)	2.25 (57.2)	.055 (1.4)	.50 (12.7)	.385 (9.8)	.316 (8.04)	.78 (19.8)	9.1 (231)	120 (534)	EXTRA HEAVY	CURVED	1.0 (454)
PLWS3EH	0.38 (9.5)	3.25 (82.6)	.055 (1.4)	.50 (12.7)	.385 (9.8)	.316 (8.04)	.78 (19.8)	12.1 (307)	120 (534)	EXTRA HEAVY	CURVED	1.3 (590)
PLWS4EH	0.38 (9.5)	4.13 (105)	.055 (1.4)	.50 (12.7)	.385 (9.8)	.316 (8.04)	.78 (19.8)	15.1 (384)	120 (534)	EXTRA HEAVY	CURVED	1.6 (726)

NOTES:

* SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION
FOR PACKAGE SIZE, PART MATERIAL, PART COLOR
AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

							TITLE						
							WIDE STRAP CABLE TIE						
							CONTROL DRAWING						
							ITEM REVISION NAME			00076SBA/06			
							DATASET FILE NAME			00076SBA_DC/06 00076SBA_REV00			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]			MATERIAL:			
							.x ± .1 [2.54] .xxx ± .005 [.127]			NYLON 6.6			
							.xx ± .01 [.25] ANGLES ± 5 °			DRAWING NUMBER:			
										THIRD ANGLE PROJECTION			
00	12/05/16	BWG	DJSL	JADE	DRAWING RELEASED	011101/00	DRAWN BY		DATE	CHK	SCALE	00076SBA_DC	
							BWG		12/5/16	DJSL	NONE	SHT 1 OF 1	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN						SIZE	
												A	

2

1

D10100DA/20

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PLWS2EH-TL350](#) [PLWS3EH-TL350](#) [PLWS4EH-TL350](#)