




PANDUIT PART NO	BUNDLE DIAM		A	B	C	D	E	F	LOOP TENSILE	CROSS SECTION	WEIGHT lbs (g) / 100 pcs	TIP STYLES
	MIN in (mm)	MAX in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	in (mm)	lbs (N)			
S12-50	.12 (3.0)	2.99 (76)	.051 (1.3)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	11.81 (300)	50 (222)	STANDARD	0.461 (209.1)	CURVED
S15-50	.12 (3.0)	4.02 (102)	.051 (1.3)	.19 (4.8)	.299 (7.6)	.23 (5.9)	.331 (8.4)	14.57 (370)	50 (222)	STANDARD	0.521 (236.3)	CURVED
S17-50	.12 (3.0)	4.33 (110)	.051 (1.3)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	16.90 (430)	50 (222)	STANDARD	0.668 (303)	STRAIGHT
S21-50	.12 (3.0)	5.51 (140)	.055 (1.4)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.326 (8.3)	20.87 (530)	50 (222)	STANDARD	.804 (364.7)	STRAIGHT

NOTE:
SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL,
PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

							TITLE					
							STRONGHOLD STANDARD TIES					
							CUSTOMER DRAWING					
							ITEM REVISION NAME			PANDUIT		
							00092FBK/00					
							DATASET FILE NAME					
							00092FBK_DC/00					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:	
							.x ± .1 [2.54] .xxx ± .020 [.51]				NYLON 6.6	
							.xx ± .02 [.5] ANGLES ± 5 °				DRAWING NUMBER:	
							 THIRD ANGLE PROJECTION				00092FBK_DC	
00	3/15/17	ACC	JSWA	JADE	DRAWING RELEASED	012502	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	ACC	2-22-17	JSWA	N/A	A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S15-50-M](#)