




PANDUIT PART NO	BUNDLE DIAM		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs(g)/100 pcs	TIP STYLE
	MIN in (mm)	MAX in (mm)										
S4-18	.06 (1.5)	.87 (22)	.044 (1.1)	.10 (2.5)	.19 (4.8)	.154 (3.9)	.181 (4.6)	3.94 (100)	18 (80)	MINIATURE	0.054 (24.3)	CURVED
S6-18	.06 (1.5)	1.57 (40)	.044 (1.1)	.10 (2.5)	.19 (4.8)	.154 (3.9)	.188 (4.8)	6.29 (160)	18 (80)	MINIATURE	0.100 (45.5)	CURVED
S8-18	.06 (1.5)	2.09 (53)	.045 (1.2)	.10 (2.5)	.19 (4.8)	.157 (4.0)	.19 (4.8)	7.87 (200)	18 (80)	MINIATURE	0.124 (56.2)	CURVED
S6-40	.08 (2.0)	1.30 (33)	.045 (1.2)	.14 (3.6)	.26 (6.6)	.19 (4.8)	.268 (6.8)	5.51 (140)	40 (178)	INTERMEDIATE	0.148 (67.4)	CURVED
S8-40	.08 (2.0)	2.09 (53)	.045 (1.2)	.14 (3.6)	.256 (6.5)	.19 (4.8)	.268 (6.8)	7.87 (200)	40 (178)	INTERMEDIATE	0.195 (88.7)	CURVED
S12-40	.08 (2.0)	2.99 (76)	.045 (1.2)	.14 (3.6)	.26 (6.6)	.181 (4.6)	.264 (6.7)	11.81 (300)	40 (178)	INTERMEDIATE	.299 (135.9)	CURVED
S15-40	.08 (2.0)	4.02 (102)	.051 (1.3)	.14 (3.6)	.232 (5.9)	.181 (4.6)	.248 (6.3)	14.57 (370)	40 (178)	INTERMEDIATE	.377 (171.1)	CURVED

NOTE:
SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL,
PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

						TITLE						
						STRONGHOLD MINIATURE AND INTERMEDIATE TIES						
						CUSTOMER DRAWING						
						ITEM REVISION NAME						
						00092FBI/00						
						DATASET FILE NAME						
						00092FBI_DC/00				MATERIAL: NYLON 6.6		
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]						
						.x ± .1 [2.54] .xxx ± .020 [.51] .xx ± .02 [.5] ANGLES ± 5 °						
00 3-15-17 ACC JSWA JADE DRAWING RELEASED						012502				DRAWING NUMBER: 00092FBI_DC		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							ACC	2-22-17	JSWA	N/A		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S6-40-M](#)