




PANDUIT PART NO	BUNDLE DIAM		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs(g)/100 pcs	TIP STYLE
	MIN in (mm)	MAX in (mm)										
S4-18	.06 (1.5)	.87 (22)	.044 (1.1)	.10 (2.5)	.19 (4.8)	.154 (3.9)	.181 (4.6)	3.94 (100)	18 (80)	MINIATURE	0.054 (24.3)	CURVED
S6-18	.06 (1.5)	1.57 (40)	.044 (1.1)	.10 (2.5)	.19 (4.8)	.154 (3.9)	.188 (4.8)	6.29 (160)	18 (80)	MINIATURE	0.100 (45.5)	CURVED
S8-18	.06 (1.5)	2.09 (53)	.045 (1.2)	.10 (2.5)	.19 (4.8)	.157 (4.0)	.19 (4.8)	7.87 (200)	18 (80)	MINIATURE	0.124 (56.2)	CURVED
S6-40	.08 (2.0)	1.30 (33)	.045 (1.2)	.14 (3.6)	.26 (6.6)	.19 (4.8)	.268 (6.8)	5.51 (140)	40 (178)	INTERMEDIATE	0.148 (67.4)	CURVED
S8-40	.08 (2.0)	2.09 (53)	.045 (1.2)	.14 (3.6)	.256 (6.5)	.19 (4.8)	.268 (6.8)	7.87 (200)	40 (178)	INTERMEDIATE	0.195 (88.7)	CURVED
S12-40	.08 (2.0)	2.99 (76)	.045 (1.2)	.14 (3.6)	.26 (6.6)	.181 (4.6)	.264 (6.7)	11.81 (300)	40 (178)	INTERMEDIATE	.299 (135.9)	CURVED
S15-40	.08 (2.0)	4.02 (102)	.051 (1.3)	.14 (3.6)	.232 (5.9)	.181 (4.6)	.248 (6.3)	14.57 (370)	40 (178)	INTERMEDIATE	.377 (171.1)	CURVED

NOTE:
SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL,
PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

						TITLE STRONGHOLD MINIATURE AND INTERMEDIATE TIES							
						CUSTOMER DRAWING							
						ITEM REVISION NAME 00092FBI/00							
						DATASET FILE NAME 00092FBI_DC/00							
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .020 [.51] .xx ± .02 [.5] ANGLES ± 5 °							
						MATERIAL: NYLON 6.6							
						DRAWING NUMBER: 00092FBI_DC							
00	3-15-17	ACC	JSWA	JADE	DRAWING RELEASED	012502							
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN	DRAWN BY ACC	DATE 2-22-17	CHK JSWA	SCALE N/A	SHT 1 OF 1	SIZE A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S8-18-M](#)