




PANDUIT PART NO	BUNDLE DIAM		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs(g)/100 pcs	TIP STYLE
	MIN in (mm)	MAX in (mm)										
S4-18	.06 (1.5)	.87 (22)	.044 (1.1)	.10 (2.5)	.19 (4.8)	.154 (3.9)	.181 (4.6)	3.94 (100)	18 (80)	MINIATURE	0.054 (24.3)	CURVED
S6-18	.06 (1.5)	1.57 (40)	.044 (1.1)	.10 (2.5)	.19 (4.8)	.154 (3.9)	.188 (4.8)	6.29 (160)	18 (80)	MINIATURE	0.100 (45.5)	CURVED
S8-18	.06 (1.5)	2.09 (53)	.045 (1.2)	.10 (2.5)	.19 (4.8)	.157 (4.0)	.19 (4.8)	7.87 (200)	18 (80)	MINIATURE	0.124 (56.2)	CURVED
S6-40	.08 (2.0)	1.30 (33)	.045 (1.2)	.14 (3.6)	.26 (6.6)	.19 (4.8)	.268 (6.8)	5.51 (140)	40 (178)	INTERMEDIATE	0.148 (67.4)	CURVED
S8-40	.08 (2.0)	2.09 (53)	.045 (1.2)	.14 (3.6)	.256 (6.5)	.19 (4.8)	.268 (6.8)	7.87 (200)	40 (178)	INTERMEDIATE	0.195 (88.7)	CURVED
S12-40	.08 (2.0)	2.99 (76)	.045 (1.2)	.14 (3.6)	.26 (6.6)	.181 (4.6)	.264 (6.7)	11.81 (300)	40 (178)	INTERMEDIATE	.299 (135.9)	CURVED
S15-40	.08 (2.0)	4.02 (102)	.051 (1.3)	.14 (3.6)	.232 (5.9)	.181 (4.6)	.248 (6.3)	14.57 (370)	40 (178)	INTERMEDIATE	.377 (171.1)	CURVED

NOTE:
SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL,
PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

						STRONGHOLD MINIATURE AND INTERMEDIATE TIES CUSTOMER DRAWING ITEM REVISION NAME 00092FBI/00 DATASET FILE NAME 00092FBI_DC/00 UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .020 [.51] .xx ± .02 [.5] ANGLES ± 5 ° THIRD ANGLE PROJECTION MATERIAL: NYLON 6.6 DRAWING NUMBER: 00092FBI_DC						
00	3-15-17	ACC	JSWA	JADE	DRAWING RELEASED	012502						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							ACC	2-22-17	JSWA	N/A		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S6-40-M0](#)