




PANDUIT PART NO	BUNDLE DIAM		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs(g)/100 pcs	TIP STYLE
	MIN in (mm)	MAX in (mm)										
S5-50	.12 (3.0)	.94 (24)	.051 (1.3)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	4.72 (120)	50 (222)	STANDARD	0.197 (89.3)	CURVED
S6-50	.12 (3.0)	1.50 (38)	.051 (1.3)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	6.30 (160)	50 (222)	STANDARD	0.262 (118.8)	CURVED
S7-50	.12 (3.0)	1.81 (46)	.051 (1.3)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	7.40 (188)	50 (222)	STANDARD	0.273 (124)	CURVED
S8-50	.12 (3.0)	2.09 (53)	.049 (1.2)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	8.46 (215)	50 (222)	STANDARD	.317 (143.8)	CURVED
S10-50	.12 (3.0)	1.97 (50)	.051 (1.3)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	9.84 (250)	50 (222)	STANDARD	0.377 (170.9)	CURVED

NOTE:
SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL,
PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

							TITLE						
							STRONGHOLD STANDARD TIES						
							CUSTOMER DRAWING						
							ITEM REVISION NAME			00092FBJ/00			
							DATASET FILE NAME			00092FBJ_DC/00			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:		
							.x ± .1 [2.54] .xxx ± .020 [.51] .xx ± .02 [.5] ANGLES ± 5 °				NYLON 6.6		
							 THIRD ANGLE PROJECTION				DRAWING NUMBER:		
											00092FBJ_DC		
00	3/15/17	ACC	JSWA	JADE	DRAWING RELEASED	012502	DRAWN BY		DATE	CHK	SCALE	SHT 1 OF 1	SIZE
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	ACC		2-22-17	JSWA	N/A		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S5-50-M](#)