




PANDUIT PART NO	BUNDLE DIAM		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT lbs(g)/100 pcs	TIP STYLE
	MIN in (mm)	MAX in (mm)										
S5-50	.12 (3.0)	.94 (24)	.051 (1.3)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	4.72 (120)	50 (222)	STANDARD	0.197 (89.3)	CURVED
S6-50	.12 (3.0)	1.50 (38)	.051 (1.3)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	6.30 (160)	50 (222)	STANDARD	0.262 (118.8)	CURVED
S7-50	.12 (3.0)	1.81 (46)	.051 (1.3)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	7.40 (188)	50 (222)	STANDARD	0.273 (124)	CURVED
S8-50	.12 (3.0)	2.09 (53)	.049 (1.2)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	8.46 (215)	50 (222)	STANDARD	.317 (143.8)	CURVED
S10-50	.12 (3.0)	1.97 (50)	.051 (1.3)	.19 (4.8)	.307 (7.8)	.23 (5.9)	.331 (8.4)	9.84 (250)	50 (222)	STANDARD	0.377 (170.9)	CURVED

NOTE:
SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL,
PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

						TITLE						
						STRONGHOLD STANDARD TIES						
						CUSTOMER DRAWING						
						ITEM REVISION NAME						
						00092FBJ/00						
						DATASET FILE NAME						
						00092FBJ_DC/00						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]						
						.x ± .1 [2.54] .xxx ± .020 [.51] .xx ± .02 [.5] ANGLES ± 5 °						
						THIRD ANGLE PROJECTION						
						MATERIAL: NYLON 6.6						
						DRAWING NUMBER: 00092FBJ_DC						
00	3/15/17	ACC	JSWA	JADE	DRAWING RELEASED	012502						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							ACC	2-22-17	JSWA	N/A		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S7-50-M](#)