




| PANDUIT<br>PART NO | BUNDLE DIAM    |                | A<br>in (mm)  | B<br>in (mm) | C<br>in (mm)  | D<br>in (mm) | E<br>in (mm)  | F<br>in (mm)  | LOOP<br>TENSILE<br>lbs (N) | CROSS<br>SECTION | WEIGHT<br>lbs(g)/100<br>pcs | TIP STYLE |
|--------------------|----------------|----------------|---------------|--------------|---------------|--------------|---------------|---------------|----------------------------|------------------|-----------------------------|-----------|
|                    | MIN in<br>(mm) | MAX in<br>(mm) |               |              |               |              |               |               |                            |                  |                             |           |
| S5-50              | .12<br>(3.0)   | .94<br>(24)    | .051<br>(1.3) | .19<br>(4.8) | .307<br>(7.8) | .23<br>(5.9) | .331<br>(8.4) | 4.72<br>(120) | 50 (222)                   | STANDARD         | 0.197<br>(89.3)             | CURVED    |
| S6-50              | .12<br>(3.0)   | 1.50<br>(38)   | .051<br>(1.3) | .19<br>(4.8) | .307<br>(7.8) | .23<br>(5.9) | .331<br>(8.4) | 6.30<br>(160) | 50 (222)                   | STANDARD         | 0.262<br>(118.8)            | CURVED    |
| S7-50              | .12<br>(3.0)   | 1.81<br>(46)   | .051<br>(1.3) | .19<br>(4.8) | .307<br>(7.8) | .23<br>(5.9) | .331<br>(8.4) | 7.40<br>(188) | 50 (222)                   | STANDARD         | 0.273<br>(124)              | CURVED    |
| S8-50              | .12<br>(3.0)   | 2.09<br>(53)   | .049<br>(1.2) | .19<br>(4.8) | .307<br>(7.8) | .23<br>(5.9) | .331<br>(8.4) | 8.46<br>(215) | 50 (222)                   | STANDARD         | .317<br>(143.8)             | CURVED    |
| S10-50             | .12<br>(3.0)   | 1.97<br>(50)   | .051<br>(1.3) | .19<br>(4.8) | .307<br>(7.8) | .23<br>(5.9) | .331<br>(8.4) | 9.84<br>(250) | 50 (222)                   | STANDARD         | 0.377<br>(170.9)            | CURVED    |

NOTE:  
SEE WWW.PANDUIT.COM FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE, PART MATERIAL,  
PART COLOR AND ANY THIRD PARTY RECOGNITION OR COMPLIANCE.

|     |         |     |      |      |                  |                                                                       |          |         |      |       |            |   |
|-----|---------|-----|------|------|------------------|-----------------------------------------------------------------------|----------|---------|------|-------|------------|---|
|     |         |     |      |      |                  | TITLE                                                                 |          |         |      |       |            |   |
|     |         |     |      |      |                  | STRONGHOLD STANDARD TIES                                              |          |         |      |       |            |   |
|     |         |     |      |      |                  | CUSTOMER DRAWING                                                      |          |         |      |       |            |   |
|     |         |     |      |      |                  | ITEM REVISION NAME                                                    |          |         |      |       |            |   |
|     |         |     |      |      |                  | 00092FBJ/00                                                           |          |         |      |       |            |   |
|     |         |     |      |      |                  | DATASET FILE NAME                                                     |          |         |      |       |            |   |
|     |         |     |      |      |                  | 00092FBJ_DC/00                                                        |          |         |      |       |            |   |
|     |         |     |      |      |                  | UNLESS OTHERWISE SPECIFIED,<br>DIMENSIONAL TOLERANCES ARE: IN [ mm ]  |          |         |      |       |            |   |
|     |         |     |      |      |                  | .x ± .1 [ 2.54 ] .xxx ± .020 [ .51 ]<br>.xx ± .02 [ .5 ] ANGLES ± 5 ° |          |         |      |       |            |   |
|     |         |     |      |      |                  | THIRD ANGLE<br>PROJECTION                                             |          |         |      |       |            |   |
|     |         |     |      |      |                  | MATERIAL:                                                             |          |         |      |       |            |   |
|     |         |     |      |      |                  | NYLON 6.6                                                             |          |         |      |       |            |   |
|     |         |     |      |      |                  | DRAWING NUMBER:                                                       |          |         |      |       |            |   |
|     |         |     |      |      |                  | 00092FBJ_DC                                                           |          |         |      |       |            |   |
| 00  | 3/15/17 | ACC | JSWA | JADE | DRAWING RELEASED | 012502                                                                |          |         |      |       |            |   |
| REV | DATE    | BY  | CHK  | APR  | DESCRIPTION      | ECN                                                                   | DRAWN BY | DATE    | CHK  | SCALE | SIZE       |   |
|     |         |     |      |      |                  |                                                                       | ACC      | 2-22-17 | JSWA | N/A   | SHT 1 OF 1 | A |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Panduit:](#)

[S6-50-M](#)