

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




M6 SPLIT LOCK WASHER (1)



M6-32 MACHINE SCREW NUT



M6 EXTERNAL TOOTH LOCK WASHER (1)



#10 AWG JUMPER WIRE ASSEMBLY (1)  
PNF10-14R (2)  
#10 AWG WIRE- GREEN & YELLOW STRIPED INSULATED (8.00" [ 203.20 ])

NOTES:

1. PANDUIT PART NO: PGKE
2. WEIGHT: .035 LB/ea  
15.95 g/ea
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.

CAD FILENAME/LAYERS

C41449\_00

**PANDUIT**

CORP. TINLEY PARK, ILLINOIS

PGKE GROUNDING KIT  
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,  
DIMENSIONAL TOLERANCES ARE:

(.X) ± (.XXX) ± .010(.3)  
(.XX) ± .03(.8) ANGLES ±

UNLESS OTHERWISE SPECIFIED,  
ALL DIMENSIONS ARE GIVEN  
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY  
KLFU

MAT'L:

SCALE

NONE

DATE  
9/04

SEE  
NOTES

DRAWING NO.

C41449

DWG  
A  
SIZE

00	9/04	KLFU		RELEASED						
REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

PGKE