


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

```

SE      12      PS - 4C      R      O
|        |        |         |       |
|        |        |         |       +----- COLOR: 0 = WEATHER
|        |        |         |               RESISTANT
|        |        |         |               BLACK
|        |        |         +----- REEL
|        |        +----- LENGTH: L = 50'   (15.2M)
|        |                   LQ = 75'   (22.9M)
|        |                   C  = 100'  (30.5M)
|        |                   CL = 150'  (45.7M)
|        |                   T  = 200'  (61.0M)
|        |                   4C = 400'  (121.9M)
|        +----- MATERIAL: PSFR = POLYETHYLENE TEREPHTHALATE
|                               (FLAME RETARDANT PET)
|                               PS  = POLYETHYLENE TEREPHTHALATE
|                                   (PET)
+----- NOMINAL DIAMETER: 12 = 0.125 (3.2)
                           25 = 0.250 (6.4)
                           50 = 0.500 (12.7)
                           75 = 0.750 (19.1)
                           100 = 1.000 (25.4)
                           150 = 1.500 (38.1)
|
+----- SLEEVING EXPANDABLE

```




PANDUIT PART NO.	NOMINAL DIAMETER (mm)	WALL THICKNESS (IN)	BUNDLE DIA.	WEIGHT/100' (LB)
SE12_____4CRO	0.125 (3.2)	0.024 (0.61)	0.09 - 0.13 (2.37 - 6.35)	0.20
SE25_____TRO	0.250 (6.35)	0.025 (0.64)	0.19 - 0.26 (4.83 - 6.35)	0.60
SE50_____CLRO	0.500 (12.7)	0.025 (0.64)	0.44 - 0.50 (11.18 - 12.70)	1.40
SE75_____CRO	0.750 (19.05)	0.025 (0.64)	0.63 - 0.75 (16.00 - 19.05)	1.60
SE100_____CRO	1.000 (25.4)	0.038 (0.97)	0.88 - 1.00 (22.35 - 25.40)	2.00
SE150_____LQRO	1.500 (38.1)	0.038 (0.97)	1.38 - 1.50 (35.05 - 38.10)	2.70

NOTES:

1. ALL STRANDS OF THE PET SLEEVING SHALL BE THE SAME COLOR.
2. THE FLAME RETARDANT PET SHALL HAVE A WHITE TRACER.
3. REELS MAY HAVE SPLICES DEPENDING ON LENGTH.

D	LENGTH	20 FT	75 FT	100 FT	150 FT	200 FT	400 FT
	MAX SPLICES	1	1	1	2	2	4
	MAX SPLICE DISTANCE (FT)	15	20	20	25	25	25

4. SE200P ONLY OFFERED IN THE STD PET MATERIALS.

							TITLE					
							PAN-WRAP BRAIDED SLEEVING					
							CUSTOMER DRAWING					
							ITEM REVISION NAME			14B208BB/01		
							DATASET FILE NAME			14B208BB_DC/01A		
1	11.19.15	BDK	MRJS	RGRO	E. UPDATED CHART D. REDESIGNED CHART C. ADDED NOTE 4 B. ADDED BUNDLE DIAMETER A. REMOVED SE38...; SE125...; SE200... AND RESPECTIVE DETAILS	14B208BB_DC	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± N/A .XXX ± N/A .XX ± N/A ANGLES ± N/A  THIRD ANGLE PROJECTION				MATERIAL: SEE PART NUMBER DESCRIPTION	
00A	7-8-14	DJSL	VJS	JADE	DRAWING RELEASED	14B208BB_DC					DRAWING NUMBER: 14B208BB_DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[SE150PS-LQR0](#) [SE12PS-4CR0](#) [SE50PSFR-CLR0](#) [SE100PSFR-CR0](#) [SE100PS-CR0](#) [SE12PSFR-4CR0](#) [SE25PS-TR0](#) [SE25PSFR-TR0](#) [SE50PS-CLR0](#) [SE75PS-CR0](#) [SE150PSFR-LQR0](#) [SE75PSFR-CR0](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[SE200PSFR-LR0](#) [SE200PS-LR0](#) [SE200PFR-TR0](#)