


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART#	DESCRIPTION	WEIGHT
NK6TM**	8 POSITION, 8 WIRE UNIVERSAL MODULE. TERMINATION CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	1.43 LB/100 PCS (649g/100 PCS)



#### NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND PACKAGE QUANTITY.
2. MATERIAL:  
MODULE HOUSING- ABS  
NOMINAL WALL THICKNESS .078(2.0).  
PRESERVATION CAP-PC
3. ALL NETKEY CAT6, 8 POSITION, 8 WIRE JACK MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION PAIR MODULAR PLUGS WITHOUT DAMAGE.
4. THIS PART IS DESIGNED FOR USE WITH STANDARD KEYSTONE OPENINGS.
5. DIMENSIONS IN PARENTHESES ARE IN METRIC.

PANEL OPENING REQUIREMENTS  
PANEL THICKNESS: .048" - .058"  
(1.22mm - 1.47mm)



PART NUMBER		NK6TM**	
TITLE		NETKEY CATEGORY 6 JACK MODULE	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		M01336EJ/00	
MATERIAL:		SEE NOTE 2	
DRAWING NUMBER:		01336-41	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]		DRAWN BY	
.X ±		DATE	
.XX ± .03 [ .8 ]		MDJR	
.XXX ± .010 [ .3 ]		5-06-03	
ANGLES ±		CHK	
THIRD ANGLE PROJECTION		REFR	
SCALE		NONE	
SHT 1 OF 1		SIZE	
A		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5-16-14	MDJR	REFR	JCK	A. UPDATED TITLE BLOCK.	01336-41
R	5-12-03	MDJR			RELEASED TO PRODUCTION	01336-41

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

NK6TMIW