





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT PART#	WEIGHT
NKUSBAA**	.02 LB/EACH PC
IAPNKUSBAAWH	(9.17 g/EACH PC)



NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [] ARE METRIC.



MODEL FILENAME		M03197AA/00	SIZE A
DRAWING FILENAME		M03197AA_DC14/00B	
NETKEY USB 2.0 FEMALE A TO FEMALE A COUPLER MODULE CUSTOMER DRAWING			
 THIRD ANGLE PROJECTION		PANDUIT® TINLEY PARK, IL 60487	
		I.I. NUMBER N/A	
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.005 (.XX) ±.01 ANGLES ± 1°		PRODUCT SPEC/ PKG SPEC N/A	
		ASSY METHOD/ TEST METHOD N/A	
DRAWN BY MDJr		SCALE 1 : 1	
DATE 8-18-09		PART NO. SEE TABLE	
CHK'D HMK		DRAWING NO. 03197-14	
MAT'L			

I	6-6-11	BJN	JCO	A. ADDED SUPPLEMENTAL P/N IAPNKUSBAAWH	03173-14	JCO	JCO		
R	9-17-09	MDJr	HMK	RELEASED TO PRODUCTION	03173-14	HMK	HMK		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[NKUSBAAWH](#) [NKUSBAABL](#) [NKUSBAAAW](#) [NKUSBAAEI](#) [NKUSBAAIG](#) [NKUSBAAIW](#)