


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



	PANDUIT PART NO.	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
		MIN. in (mm)	MAX. in (mm)										
* PLT4H-XX/147		.188 (4.8)	4.11 (104.5)	.060 (1.5)	.300 (7.6)	.338 (8.6)	.290 (7.4)	.480 (12.2)	14.5 (368)	120 (534)	HEAVY	STRAIGHT	1.03 (468)

NOTE: 1) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

2) * XX DESIGNATES PACKAGE QUANTITY AND MATERIAL TYPE.

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

							TITLE						
							PAN-TY CABLE TIES - PLT SERIES						
							CUSTOMER DRAWING						
							ITEM REVISION NAME				PANDUIT		
							W10001CL/01						
							DATASET FILE NAME				MATERIAL: NYLON 6.6		
							W10001CL/01 - SS-43005_REV01						
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ± - - - .XXX ± .020 [.51] .XX ± .02 [.5] ANGLES ± - - -						
							- THIRD ANGLE PROJECTION				DRAWING NUMBER: SS-43005		
01	10/17/14	BWG	MPH	JADE	REVISED MAX BUNDLE DIA TO REFLECT ACTUAL MEASURED DIMENSION. WAS 4.00 (102) .	SS-43005/01							
R	11/25/13	BWG	JADE	JADE	DRAWING RELEASED	SS-43005/00							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1		SIZE
							BWG	11-25-13	JADE	NONE			A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PLT4H-TL0/147](#) [PLT4H-TL30/147](#)