


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART#	DESCRIPTION	WEIGHT*
CJSQ688TGBL	8 POSITION, 8 WIRE SHIELDED MODULE WITH INTEGRAL SHIELD. TERMINATION CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	3.314 LB/100 PCS (1503g/100 PCS)

*WEIGHT IS APPROXIMATE



NOTES:

1. WHITE WIRE CAP DESIGNATES CATEGORY 6 PERFORMANCE.
2. MATERIAL:
MODULE HOUSING-ABS
NOMINAL WALL THICKNESS .078(2.0).
WIRE CAP-PC/ZINC
3. ALL PVIQ TX6 8 POSITION, 8 WIRE, KEYED JACK MODULES ARE MADE TO EXCEPT ONLY PVIQ KEYED PLUG MODULES.
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. .187 x .010" GROUNDING TAB PROVIDED AS OPTIONAL CONDUCTIVE PATH FOR GROUNDING.



ACTUAL SIZE

MODEL FILENAME		M03084EJ/00	SIZE A
DRAWING FILENAME		M03084EJ_DC56/00A	
TITLE PVIQ TX6 MODULAR KEYED SHIELDED JACK MODULE CUSTOMER DRAWING			
	PANDUIT TM CORP. TINLEY PARK, ILL 60477		I.I. NUMBER
			PRODUCT SPEC
	ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.03(.8) ANGLES ±		WORK INSTRUCTION
			SCALE FULL
DRAWN BY MDJr		REVIEW DRAWING NUMBERS	PART NO. CJSQ688TGBL
DATE 10-22-08			DRAWING NO. 03084 - 56
CHK'D			

R	1-29-10	MDJr		RELEASED TO PRODUCTION	03084-56					
REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	OTH

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

CJSQ688TGBL