







THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CMPHF2	1.4 LB/EACH PC .64 kg/EACH PC

NOTES:

- NOTES:
1. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
  2. DIMENSIONS IN PARENTHESES ARE IN METRIC.
  3. PARTS INCLUDED:
    - 4- D-RINGS
    - 1- METAL STAMPING
    - 4- 12-24 SCREWS
  4. FOR OPTIONAL SNAP ON COVER USE PART NUMBER CMPH2C.



							TITLE  OPEN CABLE MANAGEMENT PANEL HORIZONTAL FRONT ONLY (CMPHF2)  CUSTOMER DRAWING					
							ITEM REVISION NAME  M00072AC/04					
							DATASET FILE NAME  M00072AC_DC_04A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]					
04A	3-26-15	TWV	MACA	KRKE	BOM ADJUSTMENT; REVISED NOTES.	00072-16	 THIRD ANGLE PROJECTION					
02B	4-1-13	BAME	FGR	CMK	REVISED AND REDRAWN; ALL PREVIOUS REVS OMITTED	00072-16						
							MATERIAL: STAMPING - BLACK POWDER COATED STEEL				RINGS - BLACK PC	
							DRAWING NUMBER:  00072 - 16				SIZE A	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JSP	DATE 7-16-98	CHK FJD	SCALE NONE	SHT 1 OF 1	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

CMPHF2