





1

NOTES:

1. IDENTIFICATION: 1RU HORIZONTAL, (10) 5-20R
120V / 20A / SINGLE-PHASE POU

<u>PART NO.</u>	<u>COLOR</u>
CMRPSH20STL	BLACK

2. ACCESSORY COMPONENTS:
(4) 10-32 x 1/2" MOUNTING SCREWS
(4) 12-24 x 1/2" MOUNTING SCREWS
3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
4. SURGE SUPPRESSION UP TO 330V OR 720 JOULES.
5. UL® & c-UL® LISTED 60950.
6. RoHS COMPLIANT.
7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR
A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE
WITH THIS PART.
8. MAXIMUM AVAILABLE INPUT POWER = 1.9 KW
9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE
NATIONAL, STATE, AND LOCAL CODES.



MODEL FILENAME		09V098YE/00.PRT	
CAD FILENAME/LAYERS		09V098YE_DC/00A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
1RU HORIZONTAL, (10) 5-20R POWER OUTLET UNIT (CMRPSH20STL) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
[METRIC - MILLIMETER] X. +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13		ANGLE +/- 1°	
DRAWN BY MRWA		SCALE NONE	
DATE 10-26-11		DRAWING NO. 09V098YE	
CHK'D		DWG  SIZE	

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CMRPSH20STL](#)