

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

|             |               |
|-------------|---------------|
| PANDUIT P/N | WEIGHT        |
| CMRPSV15SIL | 9 lb (4.1 kg) |

NOTES:


1. IDENTIFICATION: VERTICAL, (20) 5-15R  
120V / 15A / SINGLE-PHASE POU

PART NO.  
CMRPSV15SIL




COLOR  
BLACK

2. ACCESSORY COMPONENTS:  
 (4) #10-32 x 1/2" MOUNTING SCREWS  
 (4) #12-24 x 1/2" MOUNTING SCREWS  
 (2) #10-32 LOCKING COLLAR SCREWS  
 (2) L-BRACKETS


3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
4. SURGE SUPPRESSION UP TO 330V OR 720 JOULES.
5. UL® & c-UL® LISTED 60950.
6. RoHS COMPLIANT.
7. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
8. MAXIMUM AVAILABLE INPUT POWER = 1.4 KW
9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.



TOOLLESS MOUNTING  
BUTTON 2X



PLUG  
15 AMP, 125V, SINGLE-PHASE  
STRAIGHT BLADE  
NEMA 5-15P



TWENTY (20)  
RECEPTACLES  
20 AMP, 125V  
STRAIGHT BLADE  
NEMA 5-15R

|     |          |      |      |                                                    |  |          |   |   |              |
|-----|----------|------|------|----------------------------------------------------|--|----------|---|---|--------------|
|     |          |      |      |                                                    |  |          |   |   |              |
|     |          |      |      |                                                    |  |          |   |   |              |
|     |          |      |      |                                                    |  |          |   |   |              |
|     |          |      |      |                                                    |  |          |   |   |              |
|     |          |      |      |                                                    |  |          |   |   |              |
|     |          |      |      |                                                    |  |          |   |   |              |
| 01A | 9-11-12  | PIP  | MRWA | A. ADDED NOTE #9. B. UPDATED BUTTON MOUNTING NOTE. |  | 09V098YB |   |   |              |
| 00A | 10-26-11 | MRWA | KRKE | RELEASED TO PRODUCTION                             |  | 09V098YB |   |   |              |
| REV | DATE     | BY   | CHK  | DESCRIPTION                                        |  | ECN      | - | R | CUST SUP OTH |

|                                                                                                                                                                                                                                                                        |  |                                                                                                  |  |
|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|--|--------------------------------------------------------------------------------------------------|--|
| MODEL FILENAME                                                                                                                                                                                                                                                         |  | 09V098YB/01.PRT                                                                                  |  |
| CAD FILENAME/LAYERS                                                                                                                                                                                                                                                    |  | 09V098YB_DC/01A.PRT                                                                              |  |
| <div style="font-size: 48pt; font-family: sans-serif; letter-spacing: 0.5em;">PANDUIT</div> <div style="font-size: 18pt; font-weight: bold; margin-top: 5px;">CORP</div> <div style="font-size: 14pt; margin-top: 5px;">TINLEY PARK, ILLINOIS</div>                    |  |                                                                                                  |  |
| <div style="font-size: 24pt; font-weight: bold; margin-bottom: 10px;">VERTICAL, (20) 5-15R</div> <div style="font-size: 24pt; font-weight: bold; margin-bottom: 10px;">POWER OUTLET UNIT</div> <div style="font-size: 24pt; font-weight: bold;">CUSTOMER DRAWING</div> |  |                                                                                                  |  |
| UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:<br>INCHES<br>X.X +/- 0.03<br>X.XX +/- 0.015<br>X.XXX +/- 0.005                                                                                                                                                 |  | UNLESS OTHERWISE SPECIFIED,<br>ALL DIMENSIONS ARE GIVEN IN<br>INCHES, THIRD ANGLE PROJECTION     |  |
| [METRIC - MILLIMETER]<br>X +/- 0.8<br>X.X +/- 0.4<br>X.XX +/- 0.13                                                                                                                                                                                                     |  | ANGLE<br>+/- 1°                                                                                  |  |
| DRAWN BY<br><div style="font-size: 18pt; font-weight: bold;">MRWA</div>                                                                                                                                                                                                |  | SCALE<br><div style="font-size: 18pt; font-weight: bold;">NONE</div>                             |  |
| DATE<br><div style="font-size: 14pt;">10-26-11</div>                                                                                                                                                                                                                   |  | DRAWING NO.<br><div style="font-size: 18pt; font-weight: bold; margin-top: 20px;">09V098YB</div> |  |
| CHK'D<br><div style="font-size: 14pt;">KRKE</div>                                                                                                                                                                                                                      |  | DWG<br><div style="font-size: 24pt; font-weight: bold; margin-top: 20px;">B</div>                |  |

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CMRPSV15SIL](#)