

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CMRPSV20C139TL	15 lb (6.8 kg)

NOTES:

1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19
120V / 20A / SINGLE-PHASE POU

<u>PART NO.</u>	<u>COLOR</u>
CMRPSV20C139TL	BLACK

2. ACCESSORY COMPONENTS:
 (4) #10-32 x 1/2" MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).



4. UL® & c-UL® LISTED 60950.

5. RoHS COMPLIANT.


6. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

7. MAXIMUM AVAILABLE INPUT POWER = 1.9 KW


8. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




— 10 FOOT INLET POWER CORD



PLUG
20 AMP, 125V, SINGLE-PHASE
TWIST LOCK
NEMA L5-20P



TWENTY-FOUR (24)
RECEPTACLES
15 AMP, 250V
STRAIGHT BLADE
IEC 60320/C13



SIX (6)
RECEPTACLES
20 AMP, 250V
STRAIGHT BLADE
IEC 60320/C19

01A	5-29-13	MRWA	KRKE	A. CORRECTED PART NUMBER IN NOTE 1		09V098YI					
00A	10-26-11	MRWA	KRKE	RELEASED TO PRODUCTION		09V098YI					
REV	DATE	BY	CHK	DESCRIPTION		ECN	-	R	CUST	SUP	OTH

MODEL FILENAME		09V098YI/01.PRT	
CAD FILENAME/LAYERS		09V098YI_DC/01A.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, MIXED (24) C-13 & (6) C-19 POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES [METRIC - MILLIMETER]		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
X.X +/- 0.03 X. +/- 0.8 X.XX +/- 0.015 X.X +/- 0.4 +/- 1" X.XXX +/- 0.005 X.XX +/- 0.13			
DRAWN BY MRWA		SCALE NONE	
DATE 10-26-11		DRAWING NO. 09V098YI	
CHK'D KRKE		DWG B	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CMRPSV20C139TL](#)