




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.


PANDUIT P/N	WEIGHT
CMRPSV20SILTLM	9 lb (4.1 kg)

- NOTES:
1. IDENTIFICATION: VERTICAL, (20) 5-20R, METERED
120V / 20A / SINGLE-PHASE POU
 - PART NO. CMRPSV20SILTLM COLOR BLACK
 2. ACCESSORY COMPONENTS:
(4) #10-32 x 1/2" MOUNTING SCREWS
(4) #12-24 x 1/2" MOUNTING SCREWS
(2) #10-32 LOCKING COLLAR SCREWS
(2) L-BRACKETS
 3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
 4. POWER METER - RED, 4-DIGIT LED CONTINUOUSLY SCROLLS THROUGH POWER FACTOR, AMPS, VOLTS (RMS), AND REAL POWER IN WATTS (RMS).
 5. SURGE SUPPRESSION UP TO 330V OR 720 JOULES.
 6. UL® & c-UL® LISTED 1950.
 7. RoHS COMPLIANT.
 8. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
 9. MAXIMUM AVAILABLE INPUT POWER = 1.9 KW
 10. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




TOOLLESS MOUNTING
BUTTON 2X





PLUG
20 AMP, 125V, SINGLE-PHASE
TWIST LOCK
NEMA L5-20P



TWENTY (20)
RECEPTACLES
20 AMP, 125V
STRAIGHT BLADE
NEMA 5-20R

01A	9-13-12	PIP	MRWA	A. ADDED NOTE #10.											09V098YL					
00A	10-26-11	MRWA	KRKE	RELEASED TO PRODUCTION											09V098YL					
REV	DATE	BY	CHK	DESCRIPTION											ECN	R	CUST	SUP	OTH	

MODEL FILENAME		09V098YL/01.PRT	
CAD FILENAME/LAYERS		09V098YL_DC/01A.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, (20) 5-20R, METERED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13	
ANGLE +/- 1°		ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
DRAWN BY MRWA		SCALE NONE	
DATE 10-26-11		DRAWING NO. 09V098YL	
CHK'D KRKE		DWG B SIZE	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CMRPSV20SILTLM](#)