



PANDUIT P/N	WEIGHT
CMRPSV20STL	13 lb (5.9 kg)

<u>PART NO.</u>	<u>COLOR</u>
CMRPSV20STL	BLACK


9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




20A THERMAL BREAKER



10 FOOT INLET POWER CORD



PLUG
20 AMP, 125V, SINGLE-PHASE
TWIST LOCK
NEMA L5-20P



TWENTY-FOUR (20)
RECEPTACLES
20 AMP, 125V
STRAIGHT BLADE
NEMA 5-20R

01A	9-13-12	PIP	MRWA	A. ADDED NOTE #9.	09V098YN				
00A	10-26-11	MRWA	KRKE	RELEASED TO PRODUCTION	09V098YN				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098YN/01.PRT													
CAD FILENAME/LAYERS		09V098YN_DC/01A.PRT													
PANDUIT CORP TINLEY PARK, ILLINOIS															
VERTICAL, (20) 5-20R POWER OUTLET UNIT CUSTOMER DRAWING															
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,													
INCHES <table><tr><td>X.X</td><td>+/- 0.03</td><td>X.</td><td>+/- 0.8</td></tr><tr><td>X.XX</td><td>+/- 0.015</td><td>X.X</td><td>+/- 0.4</td></tr><tr><td>X.XXX</td><td>+/- 0.005</td><td>X.XX</td><td>+/- 0.13</td></tr></table>		X.X	+/- 0.03	X.	+/- 0.8	X.XX	+/- 0.015	X.X	+/- 0.4	X.XXX	+/- 0.005	X.XX	+/- 0.13	ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
X.X	+/- 0.03	X.	+/- 0.8												
X.XX	+/- 0.015	X.X	+/- 0.4												
X.XXX	+/- 0.005	X.XX	+/- 0.13												
DRAWN BY		SCALE													
MRWA		NONE													
DATE		DRAWING NO.													
10-26-11		09V098YN													
CHK'D		DWG													
KRKE		B													
		SIZE													

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[CMRPSV20STL](#)