



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.






PANDUIT P/N	MATERIAL	WEIGHT / PC
UCIB1-V316	316 STAINLESS STEEL	103.5 g [.228 lbs]
UCIB1-VC	COMMERCIAL STEEL / GALVANIZED	107.8 g [.238 lbs]

NOTES :

1. PRIMARY DIMENSIONS IN METRIC (mm).
DIMENSIONS IN [] ARE ENGLISH [in].
2. THIS PRODUCT INTENDED FOR USE WITH
1-BEAM STYLE LADDER RUNG IN GALVANIZED
STEEL, STAINLESS STEEL, OR ALUMINUM
CONSTRUCTIONS.
3. EACH ASSEMBLY INCLUDES:
 - (1) TALL BRACKET PIECE
 - (1) RETAINER CLIP
 - (1) M8 X 1.25 X 20mm CARRIAGE BOLT
 - (1) SERRATED-FLANGE HEX NUT



										TITLE UNICLIP I-BEAM BRACKET UCIB1 			
										CUSTOMER DRAWING			
									ITEM REVISION NAME 12L025AW/04				
									DATASET FILE NAME 12L025AW_DC/04B				
-	-----	----	----	----	RELEASED TO PRODUCTION		-----	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: mm [IN] .x ± .3 [.01] .xxx ± .127 [.005] .xx ± .25 [.010] ANGLES ± 5 °  THIRD ANGLE PROJECTION				MATERIAL: SEE CHART	
1	06-12-14	RMHI	RMHI	RGRO	B. UPDATED WEIGHTS IN TABLE A. REVISED TITLE		12L025AW-DC					DRAWING NUMBER: 12L025AW-DC	
R	04-30-14	JBN	RMHI		DRAWING RELEASED								
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY JBN	DATE 04-30-14	CHK RMHI	SCALE N.T.S.	SHT 1 OF 1	SIZE A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[UCIB1-VC](#) [UCRND1-V316](#)