




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE AWG [mm ²]	TAB SIZE in. [mm]	HOUSING COLOR	MAX WIRE INSUL DIA	DIMENSIONS in. [mm]			WIRE STRIP LENGTH in. [mm] +1/32 [0,8] -0	TOOLS
					L ± .04 [1,1]	W ± .01 [0,3]	M ± .02 [0,6]		
EDV18-187MB	#22-16 [0.5-1.5]	.187 X .032 [4.8 X 0.8]	RED	0.145 [3.7]	0.75 [19.0]	0.19 [4.8]	.39 [10.0]	9/32 [6.8]	KST2000C
EDV14-187MB	#16-14 [1.5-2.5]		BLUE	0.165 [4.2]	0.75 [19.0]	0.19 [4.8]	.39 [10.0]		

NOTES:

- UL LISTED FOR:
 - STRANDED COPPER WIRE ONLY - INTERNAL WIRING
 - 167°F (75°C) MAX TEMP RATING
 - 300V MAX VOLTAGE RATING
- MATERIAL:
 - STAMPING: .016" [0.4] THICK BRASS, TIN PLATED
 - HOUSING: VINYL
- SEE www.panduit.com FOR PACKAGE QUANTITIES
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



										TITLE STRONGHOLD MALE DISCONNECTS (187 SERIES) VINYL INSULATED #22-14 AWG CUSTOMER DRAWING					
										ITEM REVISION NAME 00123SSN/00					
										DATASET FILE NAME 00123SSN_DC/00					
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °		MATERIAL: SEE NOTES			
										 THIRD ANGLE PROJECTION		DRAWING NUMBER: 00123SSN-DC			
00	2/18	JHNU	TMR	RGB	DRAWING RELEASED		00123SS			DRAWN BY JHNU	DATE -	CHK RLS	SCALE N.T.S.	SHEET 1 OF 1	SIZE A
REV	DATE	BY	CHK	APR	DESCRIPTION		ECN								

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[EDV14-187MB-Q](#) [EDV18-187MB-Q](#)