


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE AWG [mm ²]	TAB SIZE INCH [mm]	HOUSING COLOR	DIMENSIONS in. [mm]	
				L ± .03 [0,8]	MAX WIRE INSULATION DIA.
EDV18-250M	#22-18 [0,5-1,0]	.250 X .032 [6,3 X 0,8]	RED	.98 [24,9]	.154 [3,91]
EDV14-250M	#16-14 [1,5-2,5]		BLUE	.96 [24,3]	.180 [4,57]

NOTES:

1. CSA CERTIFIED FOR:
 - A. STRANDED COPPER WIRE ONLY
 - B. 221°F (105°C) MAX TEMP RATING
 - C. 600V MAX VOLTAGE
2. MATERIAL:
 - A. STAMPING: .031" (0.8) THK COPPER, NICKEL PLATED
 - B. HOUSING: VINYL
3. INSTALLATION TOOLS: CT-500, CT-550, CT-1550, CT-1551
4. WIRE STRIP LENGTH $9/32'' \begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ [7,1mm $\begin{smallmatrix} +0.8 \\ -0 \end{smallmatrix}$]
5. SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
6. DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



CERTIFIED
LR31212

TITLE		STRONGHOLD MALE DISCONNECT (250 SERIES) VINYL INSULATED, BRAZED SEAM #22-14 AWG	
ITEM REVISION NAME		00123SHZ/00	
DATASET FILE NAME		00123SHZ/00	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL:	
.x ± .1 [2.54] .xxx ± .005 [.127]		SEE NOTES	
.xx ± .01 [.25] ANGLES ± 5 °		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		SH41405	
DRAWN BY	DATE	CHK	SCALE
JHNU	2/18	TMR	NTS
SHT 1 OF 1		A	

B

A

A

A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[EDV14-250M-L](#) [EDV18-250M-L](#) [EDV14-250M-Q](#) [EDV18-250M-Q](#)