


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	WIRE RANGE AWG [mm ²]	TAB SIZE in. [mm]	COLOR	MAX. INSUL. in. [mm]	DIMENSIONS in. [mm]	
					L ± .03 [0,8]	W ± .01 [0,3]
EDV18-250P	#22-18 [0,5-1,0]	.250 X .032 [6,4 X 0,8]	RED	.13 [3,3]	.88 [22,4]	.29 [7,4]
EDV14-250P	#16-14 [1,5-2,5]		BLUE	.16 [4,1]	.88 [22,4]	.29 [7,4]

NOTES:

- USED FOR:
 - STRANDED COPPER WIRE ONLY
 - 194°F [90°C] MAX. OPERATING TEMPERATURE
 - 300 V. MAX VOLTAGE RATING
- MATERIAL:
 - STAMPING: BRASS, TIN PLATED
 - HOUSING: VINYL
 - SLEEVE: BRASS, TIN PLATED
- INSTALLATION TOOLS: CT-100A, CT-160, CT-260, CT-400, CT-1550, CT-1551, CT-2500 (CT-2550CH), CT-600A (CT-550CH)
- WIRE STRIP LENGTH: 1/4" $\begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ [6,3mm $\begin{smallmatrix} +0,8 \\ -0 \end{smallmatrix}$]
- SEE www.panduit.com FOR PACKAGE QUANTITIES INDICATED BY PART NUMBER SUFFIX
- DIMENSIONS IN BRACKETS ARE METRIC EQUIVALENT



00	2/18	JHNU	TMR	RGB	RELEASED	00123SH
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE				STRONGHOLD PIGGYBACK DISCONNECT VINYL INSULATED, METAL SLEEVE #22-14 AWG	
				CUSTOMER DRAWING	
ITEM REVISION NAME		00123STA/00			
DATASET FILE NAME		00123STA_DC/00			
<p>UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]</p> <p>.x ± .1 [2.54] .xxx ± .005 [.127]</p> <p>.xx ± .01 [.25] ANGLES ± 5 °</p>  <p>THIRD ANGLE PROJECTION</p>				MATERIAL:	
				SEE NOTES	
				DRAWING NUMBER:	
				SH41208	
DRAWN BY	DATE	CHK	SCALE	SHEET	
TMR	2/18	TMR	NTS	SHT 1 OF 1	
				A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[EDV14-250P-L](#) [EDV18-250P-L](#) [EDV14-250P-Q](#) [EDV18-250P-Q](#)