


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS - in.					TOOLS
		L ± .03	W ± .01	C ± .02	M ± .03	H ± .01	
EV18-6LFB	#6	.90 (22.9)	.27 (6.9)	.22 (5.6)	.68 (17.3)	.14 (3.6)	*CT-100A CT-600A (CT-500CH) CT-600A (CT-550CH) CT-1550 CT-1551
EV18-8LFB	#8	.97 (24.6)	.29 (7.4)	.25 (6.4)	.73 (18.5)	.16 (4.1)	
EV18-10LFB	#10	.97 (24.6)	.33 (8.4)	.25 (6.4)	.73 (18.5)	.19 (4.8)	

*CT-100A, 167°F (75°C) MAX TEMP. RATING

NOTES:

- UL LISTED AND CSA CERTIFIED FOR:
 - #22-18 AWG STRANDED COPPER WIRE
 - 221°F (105°C) MAX TEMP RATING
 - 600V MAX VOLTAGE RATING
(1000V. MAX. IN SIGNS, FIXTURES & LUMINARIES)
- MATERIAL:
 - STAMPING - .032" (.81) THK, COPPER TIN PLATED
 - HOUSING - VINYL, RED
- WIRE STRIP LENGTH: 5/16" $\begin{smallmatrix} +1/32 \\ -0 \end{smallmatrix}$ (7.9mm $\begin{smallmatrix} +0.8 \\ -0 \end{smallmatrix}$)
- SEE WWW.PANDUIT.COM FOR PACKAGE QUANTITIES
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS



TITLE		STRONGHOLD LOCKING FORK TERMINALS VINYL INSULATED, BUTTED SEAM #22-18 AWG	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		00123SHV/00	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.X ± .XX ±		SEE NOTES	
.XXX ± ANGLES ±		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		SH41288	
DRAWN BY	DATE	CHK	SCALE
JHNU	2/18	TMR	NONE
SHT 1 OF 1		A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[EV18-10LFB-L](#) [EV18-6LFB-L](#) [EV18-10LFB-Q](#) [EV18-6LFB-Q](#) [EV18-8LFB-Q](#) [EV18-8LFB-L](#)