

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	STUD SIZE	DIMENSIONS - IN.					TOOL
		A±.03	W±.01	C±.02	M±.03	H±.01	
PK2-10R	#10	1.95 (.49-.53)	.68 (.17-.27)	.58 (.14-.73)	1.61 (.40-.89)	.20 (5.08)	CT-2600 WITH DIE # CD-2600-PV2
PK2-14R	1/4"	1.95 (.49-.53)	.68 (.17-.27)	.58 (.14-.73)	1.61 (.40-.89)	.27 (6.86)	
PK2-56R	5/16"	1.95 (.49-.53)	.68 (.17-.27)	.58 (.14-.73)	1.61 (.40-.89)	.33 (8.38)	
PK2-38R	3/8"	1.95 (.49-.53)	.68 (.17-.27)	.58 (.14-.73)	1.61 (.40-.89)	.39 (9.91)	
PK2-12R	1/2"	2.04 (.51-.82)	.86 (.21-.84)	.58 (.14-.73)	1.61 (.40-.89)	.52 (13.21)	

NOTES :

1. RATED FOR:
A. #2 AWG STRANDED COPPER WIRE
2. SEE www.panduit.com FOR PART NUMBER
SUFFIX DESIGNATION FOR PACKAGE SIZE.
3. MATERIAL:
A. STAMPING - .060" (1.52) THK COPPER,
TIN PLATED
B. HOUSING - KYNAR, RED STRIPE
4. DIMENSIONS IN BRACKETS ARE IN MILLIMETERS
5. WIRE STRIP LENGTH: 1/2" +1/32" (12.7 +0.8)
-0 -0.0




LISTED
587H
E52164


BEVELED EDGE — 

RED COLOR STRIPE — 

(3 PLCS @ 120° APART)



02	5/14	JHNU	JHNU	RGB	REVISED TABLE : ADDED TOOL INFORMATION ADDED UL LOGO REVISED TITLE BLOCK	N41713BA- A41713
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE					
#2 BARREL KYNAR INSULATED RING TONGUE .550 (13.97) MAX. WIRE INSUL. DIAMETER CUSTOMER DRAWING					
ITEM REVISION NAME			PANDUIT		
N41713BA/02					
DATASET FILE NAME					
N41713BA/02					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .X ±.XXX ± .XX ±ANGLES ±  THIRD ANGLE PROJECTION			MATERIAL:		
			SEE NOTES		
			DRAWING NUMBER:		
			A41713		
DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
JHNU	2/05		N/A		A

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Panduit:

[PK2-56R-T](#) [PK2-10R-T](#) [PK2-38R-T](#) [PK2-14R-T](#) [PK2-12R-T](#)